



COAXIAL TERMINATION PRODUCTS


Wire Strippers

Coaxial Cable Strippers

These lightweight, compact strippers are inexpensive and simple to operate. The adjustable blades can be set for any depth to help assure nick-free strips to specification on a variety of coaxial cable up to 9/16 in. (14 mm) diameter. Also used for twisted-pair wire, tightly wrapped stranded cables, CATV cable, CB antenna cable, SO, SJ, SJT, and other types of flexible power cords. Each stripper comes complete with a full set of blades consisting of three straight and one round blade.

Description	Typical RG Cables	Cat. No.
Coaxial Cable Stripper, up to 1/8 in. (3.2 mm) O.D.	RG-174, RG-187	45-162 (Gray)
Coaxial Cable Stripper, 1/8 in. (3.2 mm) to 7/32 in. (5.556 mm) O.D.	RG-58, CB Antenna Cable	45-163 (Blue)
Coaxial Cable Stripper, 1/4 in. (6.4 mm) to 9/16 in. (14.3 mm) O.D.	RG-8	45-164 (Blue)
Cable Stripper, 3/16 in. (4.8 mm) to 5/16 in. (8 mm) O.D.	RG-59, UTP Cable	45-165 (Black)
Replacement Blade Set* for 45-162, 45-163, 45-165		L-9225
Replacement Blade Set* for 45-164		L-9226

*A set of blades consists of three straight blades and one round blade.




45-162

Coaxial Strip & Crimp Tool

This versatile tool cuts, strips and crimps connectors on RG-59 and RG-6 coaxial cable. No need to carry separate tools for each operation.

- Extremely durable blades cut copper-coated steel conductors.
- Two precision form-ground stripping holes remove the outer PVC or polyethylene jacket material from either RG-59 or RG-6 cable.
- A third stripping hole removes the inner plastic insulation from either RG-59 or RG-6 cable, without nicking the center conductor
- Two crimping nests are marked for cable size, and perform a "one-squeeze" crimp on standard "F" series fasteners.
- A third nest crimps ring terminals, or can also be used to grasp RG-6 cable and aid in connector installation.
- Has comfortable, cushioned grips.

Description	Cat. No.
RG-59 & RG-6 Coax Strip & Crimp Tool	30-433




Wire Strippers

Round Cable Slitting and Ringing Tool

The Round Cable Slitting and Ringing Tool can be used on single or multiple conductor cable up to 1.75 in. O.D. The blade can be adjusted for jacket thicknesses up to .125 in. The blade can cut around the cable jacket as well as slit the length of the cable jacket for easy removal. A spare blade is stored in the handle base.

Description	Cat. No.
Round Cable Slitting and Ringing Tool	45-144
Cable Stripper for 1/4 in. to 3/4 in. O.D.	45-128
Replacement Blades for 45-144 (2/pkg.)	LB-1748
Replacement Blades for 45-128 (2/pkg.)	L-7486



45-144

45-128