

RC-00000001100 - Housing for circular connector



1592535

<https://www.phoenixcontact.com/gb/products/1592535>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing for circular connector, series: RC, straight, Screw locking mechanism, M23, shielded: no. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives. Alternative products: 1554098

Commercial data

Item number	1592535
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	ABRAFE
Product key	ABRAFE
GTIN	4046356191418
Weight per piece (including packing)	72.72 g
Weight per piece (excluding packing)	68.18 g
Customs tariff number	85389099
Country of origin	DE

RC-00000001100 - Housing for circular connector



1592535

<https://www.phoenixcontact.com/gb/products/1592535>

Technical data

Product properties

Product type	Circular connector housing
Series	RC
Application	Signal
Shielded	no
Thread type	M23

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Rotating parts	CuZn
Gasket and O-ring material	FPM

Connector

Type	straight
------	----------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

RC-00000001100 - Housing for circular connector



1592535

<https://www.phoenixcontact.com/gb/products/1592535>

Classifications

ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

ETIM

ETIM 10.0	EC003556
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

RC-00000001100 - Housing for circular connector



1592535

<https://www.phoenixcontact.com/gb/products/1592535>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c142e0de-2986-4ec9-8e7e-b71dd34c8bee

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk