



### Main

|                           |                                                        |
|---------------------------|--------------------------------------------------------|
| Range                     | Acti9                                                  |
| Product name              | Acti9 Isobar B                                         |
| Product or component type | Loose enclosure                                        |
| Device application        | Distribution                                           |
| Provided equipment        | 1 DIN rail<br>Door<br>Slotted front cover<br>enclosure |

### Complementary

|                           |                                                |
|---------------------------|------------------------------------------------|
| Enclosure mounting        | Surface                                        |
| Number of ways            | 34 (1P)                                        |
| Number of horizontal rows | 2                                              |
| Enclosure material        | Folded sheet steel: RAL 9001 epoxy powder coat |
| Height                    | 538 Mm                                         |
| Depth                     | 138 Mm                                         |
| Width                     | 470 Mm                                         |

### Environment

|                         |                                |
|-------------------------|--------------------------------|
| IP degree of protection | IP3x conforming to BS EN 60529 |
|-------------------------|--------------------------------|

### Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Height             | 18.0 Cm    |
| Package 1 Width              | 49.0 Cm    |
| Package 1 Length             | 54.0 Cm    |
| Package 1 Weight             | 10.101 Kg  |
| Unit Type of Package 2       | PAM        |
| Number of Units in Package 2 | 24         |
| Package 2 Height             | 112.0 Cm   |
| Package 2 Width              | 100.0 Cm   |
| Package 2 Length             | 120.0 Cm   |
| Package 2 Weight             | 257.424 Kg |

### Environmental data

|                                                       |                                                                                                                             |
|-------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Packaging without single use plastic                  | No                                                                                                                          |
| Packaging made with recycled cardboard                | No                                                                                                                          |
| China RoHS Regulation                                 | <a href="#">China RoHS Declaration</a>                                                                                      |
| Environmental Disclosure                              | <a href="#">Product Environmental Profile</a>                                                                               |
| Circularity Profile                                   | No need of specific recycling operations                                                                                    |
| WEEE                                                  | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Halogen content performance                           | Halogen free plastic parts product                                                                                          |
| Take-back                                             | No                                                                                                                          |
| Carbon footprint (kg.eq.CO2 per CR, Total Life cycle) | 187                                                                                                                         |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

|                                             |
|---------------------------------------------|
| Product Life Status : <b>Commercialised</b> |
|---------------------------------------------|