

SETS 10 (3/8") METRIC


10 **3/8"**

www.gedore.com

30 JMU / D 30 JMU

SOCKET SET 3/8" 16 pieces

- ✔ With forged, tempered hexagon (no. 30) or bi-hexagon (no. D 30) UD profile sockets, hand-operated
- ✔ With accessories made from GEDORE vanadium steel 31CrV3
- ✔ With reversible with lever change ratchet
- ✔ In GEDORIT blue sheet steel case
- ✔ Dimensions: 290 x 132 x 55 mm











30 JMU-10



D 30 JMU-10

 mm

Code	No.	Ratchet	Sockets	Accessories			£
2682885	30 JMU-10	 U-10 3093 U-10	 30 6 7 8 9 10 11 12 13 14 15 16 17 18 19	 3090-5	2.2	1	
2682893	D 30 JMU-10	 U-10 3093 U-10	 D 30 6 7 8 9 10 11 12 13 14 15 16 17 18 19	 3090-5	2.3	1	

30 GMU / D 30 GMU

SOCKET SET 3/8" 17 pieces

- ✔ With forged, tempered hexagon (no. 30) or bi-hexagon (no. D 30) UD profile sockets, hand-operated
- ✔ With accessories made from GEDORE vanadium steel 31CrV3
- ✔ Set U-3 with fine toothed, dial change ratchet
- ✔ Set U-10 with reversible with lever change ratchet
- ✔ In GEDORIT blue sheet steel case
- ✔ Dimensions: 320 x 210 x 55 mm

























U-10



U-3

 mm

Code	No.	Ratchet	Sockets	Accessories			£
6235980	30 GMU-3	 U-3 3093 U-3	 30 6 7 8 9 10 11 13 14 15 16 17 19	 3087  3090-5 -10  3095	2.6	1	
6235710	30 GMU-10	 U-10 3093 U-10	 30 6 7 8 9 10 11 13 14 15 16 17 19	 3087  3090-5 -10  3095	2.7	1	
6240200	D 30 GMU-3	 U-3 3093 U-3	 D 30 6 7 8 9 10 11 13 14 15 16 17 19	 3087  3090-5 -10  3095	2.7	1	
6239380	D 30 GMU-10	 U-10 3093 U-10	 D 30 6 7 8 9 10 11 13 14 15 16 17 19	 3087  3090-5 -10  3095	2.7	1	



3/8"

i THE GEDORE SOCKET SET

- ▶ Innovative, functional design
- ▶ Sheet steel case - inside-folded, seamless edge provides added strength. The tool and foam inserts are secured to prevent them being lost
- ▶ ABS plastic tool insert, resistant to oils and greases
- ▶ Tool insert with the socket sizes permanently laser marked
- ▶ With the lid closed, the tools sit securely in their pockets
- ▶ Boxes designed so that they can be stacked easily
- ▶ Large, rounded fasteners can be opened and closed even when the user is wearing gloves
- ▶ Contoured carry handle ensures comfortable carrying even for long periods
- ▶ Environmentally-friendly powder-coated in GEDORIT blue



3/8"

30 HMU / D 30 HMU

SOCKET SET 3/8" 22 pieces

- ▶ With forged, tempered hexagon (no. 30) or bi-hexagon (no. D 30) UD profile sockets, hand-operated
- ▶ With accessories made from GEDORE vanadium steel 31CrV3
- ▶ Set U-3 with fine toothed, dial change ratchet
- ▶ Set U-10 with reversible with lever change ratchet
- ▶ In GEDORIT blue sheet steel case
- ▶ Dimensions: 320 x 210 x 55 mm

10

3/8"



U-10



U-3

mm

Code	No.	Ratchet	Sockets	Accessories	mm	£
6238300	30 HMU-3	U-3 3093 U-3	30 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22	3087 3090-5 -10 3095	3.0	1
6235470	30 HMU-10	U-10 3093 U-10	30 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22	3087 3090-5 -10 3095	3.0	1
6240470	D 30 HMU-3	U-3 3093 U-3	D 30 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22	3087 3090-5 -10 3095	3.1	1
6239700	D 30 HMU-10	U-10 3093 U-10	D 30 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22	3087 3090-5 -10 3095	3.1	1