

### FR10 - Modaflame Knit FR Long Sleeve Polo Shirt

**Collection:** Modaflame™ Knit

**Range:** Flame Resistant Multi-Norm

**Shell Fabric:** Modaflame Knit: 60% Modacrylic, 39% Cotton, 1% Carbon Fibre, 200g

**Outer Carton:** 36



#### Product information

Convenient for cooler weather and ideal for workers in industries exposed to heat. The stylish design of the garment has a 3-button placket, finished with a ribbed collar and cuffs.

#### Modaflame™ Knit

Constructed from an inherently fire resistant yarn of 60% Modacrylic, 39% Cotton and 1% Carbon Fibre. Modaflame™ Knit is strong, durable, and highly innovative. The high performance fibres are blended without any chemical treatment giving Modaflame™ Knit it's unparalleled soft, natural touch and appearance.

#### Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

#### Standards

EN ISO 11612 (A1, B1, C1, F1)

EN 1149-5

IEC 61482-2 IEC 61482-1-1 (ELIM 4.4 CAL/CM<sup>2</sup>, EBT 5.5 CAL/CM<sup>2</sup>)

IEC 61482-2 IEC 61482-1-2 APC 1

ASTM F1959/F1959M-12 (EBT = 4.3 CAL/CM<sup>2</sup> (HAF = 66%))

#### Features

- Inherent flame resistant qualities will not diminish with washing
- Protection against radiant, convective and contact heat
- High cotton content for superior comfort
- Button placket opening
- Ribbed cuffs for added comfort
- Ribbed collar
- Outstanding colour fastness and shrinkage results
- 40+ UPF rated fabric to block 98% of UV rays
- Suitable for use in ESD environments
- Suitable to be worn in an ATEX environment
- CE-CAT III

**FR10 - Modaflame Knit FR Long Sleeve Polo Shirt**  
**Commodity Code: 6105201000**

**Test House**

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)  
 Bracetown Business Park  
 D15 YN2P, Ireland  
 Cert No: 2777/13282-05/E00-00

**Wash Care**



**Carton Dimensions/Weight**

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	GTIN/DUN14
FR10TARS	Tan	55.0	36.0	34.0	0.3600	0.0673	5036108446131	25036108933413
FR10TARM	Tan	55.0	36.0	34.0	0.4080	0.0673	5036108446124	25036108933406
FR10TARL	Tan	55.0	36.0	34.0	0.4280	0.0673	5036108446117	25036108933390
FR10TARXL	Tan	55.0	36.0	34.0	0.4360	0.0673	5036108446148	25036108933420
FR10TARXXL	Tan	55.0	36.0	34.0	0.3980	0.0673	5036108446162	25036108933444
FR10TARXXXL	Tan	55.0	36.0	34.0	0.4620	0.0673	5036108446179	25036108933451
FR10TAR4XL	Tan	55.0	36.0	34.0	0.4880	0.0673	5036108446094	25036108933376
FR10TAR5XL	Tan	55.0	36.0	34.0	0.5000	0.0673	5036108446100	25036108933383