

## 3M™ Fibrlok™ Splice Kit 2559 and 2559-C

The 2559 and 2559-C Fibrlok Splice Kits are the right tools for splicing of flat cleave Fibrlok splices. If angle cleave splice connections are required in order to reduce the return loss at temperature extremes in analog networks, then the 3M Angle Splice Kit 2535 together with angle cleave Fibrlok splices (2529-AS and 2540-AS) must be used.

### Description:

- Two different light weight tool kits are available to splice the 3M Fibrlok mechanical splices
- The 2559 Kit comes without cleaver, whereas the 2559-C contains the 2534 Cleaver for flat cleaving.
- Both kits contain all required tools for easy field installation of both flat cleave Fibrlok splices, the 2529 and the 2549-G as well as the 2539 Fibrlok Splice Holder.
- As a courtesy there are complementary samples of both Fibrlok splices as well as Fibrlok Splice Holders in each tool kit (6 ea of 2529, 5 each of 2540-G, 2 ea of 2539).

### Features

- All tools for both 3M Fibrlok splices included
- Light weight, compact design
- Available with or without cleaver
- Splice samples included

### Benefits


- Universal tool kit that saves cost
- Easy to operate also in different locations
- Low investment if cleaver is already existant
- Ready to fix the problem as emergency kit

### Standards

### Applications

- Inside or outside building
- Fibre closures and terminals
- FTTP drop cables

Technology built for business



# Ordering Information

	Ref. No.
<b>Assembly tool for 2540-G Fibrlok 250µm</b> 1/pkg	2504-G
<b>Assembly Tool for 2529 Universal Fibrlok</b> 1/pkg	2501
<b>Fibrlok Splice Kit without cleaver</b> 1/pkg	2559
<b>Fibrlok Splice Preparation Kit with 2534 Cleaver</b> 1/pkg	2559-C
<b>Fibre Cleaver</b> 1/pkg	2534
<b>Universal Fibre Stripping Tool</b> 1/pkg	6365-ST
<b>Aramide Snips</b> 1/pkg	6365-KS
<b>Lint Free Cloth</b> 100ea/pack	05-00017
<b>Cleaning Alcohol Bottle</b>	VOL-0560R
<b>Instruction Manual</b>	



**3M Telecommunications**  
**3M United Kingdom plc**  
 3M Centre  
 Cain Road  
 Bracknell  
 Berkshire RG12 8HT

**3M Customer Contact Centre**  
 3M Telecommunications  
 3M United Kingdom plc  
 Tel: 0870 609 4639  
 Email: 3Melectrouk@mmm.com  
 www.3M.co.uk/telecommunications

3M and Volition are trademarks of the 3M Company. Please recycle. Printed in UK. © 3M 2012. All rights reserved to make technical alterations.

## Important notice

The details contained in this literature have been carefully prepared from information available to 3M at the time of its production. However, it is not intended to be relied upon for purposes of product specification and you should contact your sales representative if specification details are required. Because of the wide variety of processes and conditions in liability relating to 3M products are governed by the selling 3M subsidiaries in Terms of Sale subject where applicable to the prevailing law.