

Shrink sleeve - WMS 4,8 (60X9)R YE - 0800400

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Shrink sleeve, Roll, yellow, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Perforated, Mounting type: Slide on, Cable diameter: 1.6-4.8 mm, Lettering field: 60 x 9 mm



Why buy this product

- ✓ The sleeves remain flexible after shrinking
- ✓ The sleeves are pre-assembled for optimum use of material
- ✓ WMS ... shrink sleeves provide permanent and captive conductor and cable marking
- ✓ The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- ✓ The shrink sleeves provide additional electrical insulation and mechanical protection for the conductors
- ✓ Up to four markers per sleeve are separated by perforations

Key commercial data

Packing unit	1 pc
GTIN	 4 046356 626675
Weight per Piece (excluding packing)	303.1 g
Custom tariff number	39173200
Country of origin	China

Technical data

Dimensions

Length (b)	60 mm
Width (a)	9 mm

Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

General

Color	yellow
Base element material	polyolefine
Components	Halogen-free
Material	Polyolefine
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	250

Shrink sleeve - WMS 4,8 (60X9)R YE - 0800400

Technical data

General

Number of individual labels per row	1
-------------------------------------	---

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27400401
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 110 mm, color: black

Shrink sleeve - WMS 4,8 (60X9)R YE - 0800400

Accessories

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 64-WMSU WH - 0801361



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 64 mm, color: white

Ink ribbon - THERMOMARK-RIBBON 110-WMSU WH - 0801359



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 110 mm, color: white

Printing system accessories

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm
