

# Product data sheet

Specifications



Repacked Socket-outlet, Alrea, 2P with shutters, mechanism screwless, polar white

ALB61274PW



This repacked option saves 0.222 over the standard condition

## Main

|                            |                  |
|----------------------------|------------------|
| Range of product           | Alréa            |
| Product or component type  | Socket-outlet    |
| Device presentation        | Mechanism        |
| Outlet poles configuration | 2P with shutters |
| Outlet standard deviation  | French           |

## Complementary

|                         |                        |
|-------------------------|------------------------|
| Wiring device mounting  | Surface                |
| Rated current           | 16 A at 250 V AC       |
| Colour tint             | Polar white (RAL 9003) |
| fixing mode             | Screws                 |
| Connections - terminals | Screwless terminals    |
| Height                  | 62 mm                  |
| Width                   | 62 mm                  |
| Depth                   | 35 mm                  |

## Environment

|                         |      |
|-------------------------|------|
| IP degree of protection | IP20 |
| IK degree of protection | IK02 |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 5.000 cm  |
| Package 1 Width              | 6.500 cm  |
| Package 1 Length             | 9.000 cm  |
| Package 1 Weight             | 40.000 g  |
| Unit Type of Package 2       | S01       |
| Number of Units in Package 2 | 10        |
| Package 2 Height             | 15.000 cm |
| Package 2 Width              | 15.000 cm |
| Package 2 Length             | 40.000 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                  |           |
|------------------|-----------|
| Package 2 Weight | 585.000 g |
|------------------|-----------|

## Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 18 |
|----------------------|----|



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

Lower carbon footprint

0.2 kg CO2 eq.

## Use Better



### Materials and Substances

SCIP Number

52b60409-d705-46c7-9ba3-cc3ef6e307da

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

## Use Longer



### Lifetime extension

Repair

No

## Use Again



### Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins