

## Flush Strain Relief Boots for XL Cable



### **Flush Strain Relief Boots for Extra Large Cable (PS3\*?)**

Patented solution enables low profile cable assemblies (eg of Cat 6A) even with large OD cables

#### **Features**

- Designed in combination with plug [PGScbXL](#) – locks on for a flush and secure finish.
- Compact, durable construction.
- Supplied in both black and transparent versions
- Available in variations for both 7.5mm and 8.5mm cable.
- Hood extends to cover plug latch to prevent snagging on other cables.

#### **Specifications**

- Weight: 0.5g
- Material: Polycarbonate.
- Dimensions (W x H x D): 11.6 x 17 x 22.6mm

**Packaging:** Packaged in poly bags of 100 pieces.

**Commodity code:** 85176990











Code	Colour	Cable Size	EAN Number
PS3bk7.5	Black	7.5mm	5055386509727
PS3bk8.5	Black	8.5mm	5055386509734
PS3CLR7.5	Transparent	7.5mm	5055386509741
PS3CLR8.5	Transparent	8.5mm	5055386509758

ROHS Compliant

**Code: PS3\*?**

\* = bk or CLR  
? = 7.5 or 8.5



$\varnothing A = 8.50 \pm 0.10 \text{ mm}$

$\varnothing A = 7.50 \pm 0.10 \text{ mm}$

## Combined Plug and Boot for XXL Cable



### **Combined Plug and Boot for XXL Cable (PGScb7.5XCLR#20, PGScb8.5CLR#20)**

High-performance shielded plug and boot combination designed for extra-large outer diameter cable for Category 6 and 6A. The patented design allows for the plug and boot to have an extremely low profile and a secure fit.

#### **Features**

- Plug and boot designed uses patented technology in order for the boot and plug to fit securely together.
- Designed for Category 6 and 6A performance.
- Suitable for extra-large cable (eg Cat 6A and Cat 7) up to 8.5mm OD and cores up to 1.45mm OD.
- 3 prong contacts for solid and stranded cable.
- 2-part, shielded plug compliant with standards of POE.
- High-quality, durable boot made of transparent polycarbonate (also available in black - PS3bk7.5 and PS3bk8.5)
- See PGScbXL (plug) and PS3CLR (boot) for separate items.

#### **Specifications**

- Weight: 2.5g
- Dimensions (L x W x H): 30 x 11.7 x 17mm (approx.)
- Colour: Transparent boot with metal, shielded plug.
- Material:
  - Boot: Polycarbonate
  - Plug:
    - Contacts: 50 $\mu$ "/1.27 $\mu$ m gold plated Phosphor Bronze.
    - Housing: Polycarbonate UL94V-0.
    - Shielding: Nickle-plated brass.

**Packaging:** Packaged in poly bags of 20 complete sets.

**EAN Numbers:**

PGScb7.5CLR: 5055386509772

PGScb8.5CLR: 5055386509789

**Commodity code:** 85444920



Illustrative photo of latch mechanism which ensures secure and flush fit.

19/01/22