



## ROLINE Serial Printer Cable, 9 – 25-Pole

- Cable with 9-pole D-Sub socket and 25-pole D-Sub plug
- Moulded connector casings
- Connects PC with serial printer
- Screen line connected with the foil screen and both connectors

- High screening prevents data loss and electro-magnetic interference

9- pole F 1|2|3| 4 |5|7|6|8  
25pole M 4|2|3|5|6|7|8| 20

Order-No. – Packing Unit

ROLINE Serial Printer Cable, DB9 F – DB25 M	1.8m	<b>11.01.4618 – 50</b>
ROLINE Serial Printer Cable, DB9 F – DB25 M	3m	<b>11.01.4630 – 50</b>



## VALUE KVM – Combicable

- The easy way to connect your Switch with VGA / Keyboard / Mouse to the PCs
- The models tie the often separate cables like Keyboard / Monitor / Mouse cable into one cable

Cable Type	Combination	Connection PC	/	Connection Switchbox
11.99.5450 / .5455	A / B	HD15 M, 2x PS/2 M	/	HD15 F, 2x PS/2 M
11.99.5451 / .5456	A / A	HD15 M, 2x PS/2 M	/	HD15 M, 2x PS/2 M
11.99.4692 / .4693	C / D	HD15 M, USB Type A M	/	HD15 F, USB Type B M
11.99.4752 / .4753	E / E	DVI M, 2x PS/2 M	/	DVI M, 2x PS/2 M
11.99.4792 / .4793	F / G	DVI M, USB Type A M	/	DVI M, USB Type B M

Order-No. – Packing Unit

VALUE KVM Combi Cable, PS/2 + VGA (M / F)	1.8m	<b>11.99.5450 – 25</b>
VALUE KVM Combi Cable, PS/2 + VGA (M / F)	3.0m	<b>11.99.5455 – 20</b>
VALUE KVM Combi Cable, PS/2 + VGA (M / M)	1.8m	<b>11.99.5451 – 25</b>
VALUE KVM Combi Cable, PS/2 + VGA (M / M)	3.0m	<b>11.99.5456 – 20</b>
VALUE KVM Combi Cable, USB + VGA (M / F)	1.8m	<b>11.99.4692 – 25</b>
VALUE KVM Combi Cable, USB + VGA (M / F)	3.0m	<b>11.99.4693 – 20</b>
VALUE KVM Combi Cable, DVI / DVI M + PS/2	1.8m	<b>11.99.4752 – 25</b>
VALUE KVM Combi Cable, DVI / DVI M + PS/2	3.0m	<b>11.99.4753 – 20</b>
VALUE KVM Combi Cable, DVI / DVI + USB	1.8m	<b>11.99.4792 – 25</b>
VALUE KVM Combi Cable, DVI / DVI + USB	3m	<b>11.99.4793 – 20</b>

## ROLINE KVM – Cable

- The elegant and professional way to connect VGA / Keyboard / Mouse switches to PCs
- The models tie the separate cables Keyboard / Monitor / Mouse cable into one cable



Cable type	Description
11.01.5450 / 11.01.5455 / 11.01.5460	HD15 M – F, PS/2 M – M, PS/2 M – M

Order-No. – Packing Unit

ROLINE KVM-Cable PS2+VGA (M – F)	1.8m	<b>11.01.5450 – 25</b>
ROLINE KVM-Cable PS2+VGA (M – F)	3m	<b>11.01.5455 – 20</b>
ROLINE KVM-Cable PS2+VGA (M – F)	6m	<b>11.01.5460 – 10</b>

