

## Flat-Screen TV Wall Mount - Tilting

Product ID: FPWTLTB1



Save space and create an impressive display by wall-mounting a large TV in a boardroom or customer-facing area. This tilting flat-screen TV wall mount securely supports a TV up to 100" and features an attractive low-profile design.

### Create an Engaging Display for Digital Signage

Mount your large flat-screen TV in a location that's convenient for visitors, clients and employees. Create an engaging display to keep guests informed or entertained, ideal in lobbies, lecture halls, restaurants, health care centers and other meeting spaces.

The television wall mount supports most 60" to 100" (812.8 to 1778 mm) LED or LCD flat panel TVs weighing up to 165 lb. (75 kg). It also supports curved TVs, with a compatible VESA mount up to 900x600.

## **Tilting Design for Optimal Viewing**

Find the ideal viewing angle. The tilting TV wall mount lets you tilt your display up (maximum 5 degrees) or down (maximum 10 degrees) with ease.

## **Low-Profile Design**

Save space with this slim TV wall mount. With its low-profile design, your TV sits just 3.3" (85 mm) from the wall.

## **Robust Steel Construction and Easy Installation**

The heavy-duty TV mounting bracket securely supports your large flat-screen TV and is easy to install. The spring locks allow quick attachment and release. The open architecture provides ventilation and easy access to wires.

FPWTLTB1 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Securely wall-mount your TV in boardrooms, classrooms and meeting spaces
- Keep visitors informed in hotels, restaurants, commercial facilities and other venues
- Wall-mount your TV in your home theater or living room

### Features

- Heavy-duty TV wall mount fits most 60" - 100" TVs up to 165 lb. (75 kg)
- Smooth +5° / -10° tilt for the ideal viewing angle
- Fits curved TVs, with compatible VESA mount
- Space-saving low profile design sits just 3.3" (85 mm) from the wall
- Spring locks for quick attachment and release

<b>Hardware</b>	Warranty	2 Years
	# of Displays Supported	1
	Cable Management	No
	VESA Hole Pattern(s)	200x200 mm
		300x200 mm
		300x300 mm
		400x200 mm
		400x300 mm
		600x400 mm
		600x600 mm
800x600 mm		
900x600 mm		
Wallmountable	Yes	
<b>Performance</b>	Anti-theft	No
	Fits Curved TV	Yes
	Maximum Display Size	100"
	Minimum Display Size	60"
	Tilt	+ 5° / - 10°
	Video Wall	No
	Weight Capacity (Per Display)	165.8 lb [75 kg]
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel and Plastic
	Product Height	2 in [50 mm]
	Product Length	37.6 in [954 mm]
	Product Weight	9.9 lb [4.5 kg]
	Product Width	24.6 in [625 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	10.5 lb [4.8 kg]
<b>What's in the Box</b>	Included in Package	1 - Wall Bracket
		2 - Vertical Brackets
		2 - Tilt-Adjustment Knobs

- 1 - Bubble Level
- 4 - M5 x 14 Screws
- 4 - M6 x 14 Screws
- 4 - M6 x 30 Screws
- 4 - M8 x 30 Screws
- 4 - M8 x 50 Screws
- 4 - Rectangular Washers
- 8 - Small Spacers
- 8 - Large Spacers
- 6 - Wall Screws
- 6 - Concrete Anchors
- 6 - Round Washers
- 1 - Instruction Manual

---

Product appearance and specifications are subject to change without notice.