

Datasheet

5A Tan Automotive Blade Fuse, 32V

RS Stock number [563-536](#)

Automotive Fuses:



AUE Midget Car Fuses

- 10.3øx38.1 mm (13/32x1-1/2 inch)
- **Ampere Rating:** 1,2,3,4,5,6,7-1/2, 10,15,20,25,30,35,40,50,60,70,80A
- **Voltage Rating:** 32V/125V/250V
- **Caps:** Gold Finish For High Performance
- Equivalent **AGU** and **5AG** Fuses
- **Option:** Gold Plated Wire Element Available Inside With Indicator Light 30A and less

• Approvals:



CBC European Car Bakelite Fuses

- 6ø x 25mm
- **Voltage Rating:** 32V and less

Ampere Rating	Body Color
5A	Yellow
8A	White
16A	Red
20A	Beige
25A	Blue
30A	Green

- Equivalent **GBC** Fuses



AST (mini-blade type) Terminal Car Fuses

- Transparent Body
- **Voltage Rating:** 32V and less

Ampere Rating	Body Color
2A	Gray
3A	Violet
4A	Pink
5A	Tan
7-1/2A	Brown
10A	Red
15A	Lt. Blue
20A	Yellow
25A	Natural
30A	Lt. Green

- Equivalent **MIN** and **ATM** Fuses

RoHS





ATQ (blade type) Terminal Car Fuses

- Transparent Body
- **Voltage Rating:** 32V and less

Ampere Rating	Body Color
2A	BlackishGreen
3A	Violet
4A	Pink
5A	Tan
7-1/2A	Brown
10A	Red
15A	Lt. Blue
20A	Yellow
25A	Natural
30A	Lt. Green
35A	Purple

RoHS



- Equivalent **ATO** and **ATC** Fuses
- **Option:** Gold Plated Terminal Available



AMT (max-blade type) Terminal Car Fuses

- Transparent Body
- **Voltage Rating:** 32V and less

Ampere Rating	Body Color
20A	Yellow
30A	Lt. Green
35A	Lt. Red
40A	Orange
50A	Red
60A	Lt. Blue
70A	Tan
80A	Transparent

- Equivalent **MAXI** and **MAX** Fuses
- **Option:** Gold Plated Terminal Available



ANE Gold Plated High Performance Fuses

- Visible Through Mica Window
- Metal Element are 24 Kt, Gold Plated
- **Voltage Rating:** 32V
- **Ampere Rating:** 60,70,80,100, 130,150,175,200,225,250,275, 300,325,350,400,500
- Equivalent ANL Fuses
- **Option:** Other Colors for Housing Are Available
- High Performance Good For High Power Audio Systems Also Use For Lift trucks And Other Battery Operated Systems



ALF Fuse Links – Protect Wiring Harness

- Female Type Connection
- **Voltage Rating: 32V**

Ampere Rating	Body Color
20A	White
30A	Pink
40A	Green
50A	Red
60A	Yellow
80A	Black
100A	Blue

- Equivalent **FLF** Fuses
- Visible Through Transparent Cover



ALM Fuse Links – Protect Wiring Harness

- Male Type Connection
- **Voltage Rating: 32V**

Ampere Rating	Body Color
20A	White
30A	Pink
40A	Green
50A	Red
60A	Yellow
80A	Black
100A	Blue

- Equivalent **FLF** Fuses
- Visible Through Transparent Cover