



109-35-4

1/4" Socket Hex & Bit Set Metric, 35 Pcs






### PRODUCT DETAILS

- 1/4" socket set 35 pcs
- Hex sockets, metric sizes
- Chrome vanadium alloy steel
- Chrome plated bright finish
- High density polyethylene box
- Standards: DIN 3120, DIN 3124, DIN 3122



### PRODUCT ATTRIBUTES

| Product  |  |  |  |
|----------|---|--|---|
| 109-35-4 | 35  | 60 x 170 x 250 mm  | 1200 g  |

## SET CONTENT



Hex Key Nickel Plated 1.5 mm  
**040001**



Hex Key Nickel Plated 2 mm - 5/64"  
**040011**



Hex Key Nickel Plated 2.5 mm  
**040021**



Socket 1/4" Hex 4 mm  
**101-04-1**



Socket 1/4" Hex 4.5 mm  
**101-045-1**



Socket 1/4" Hex 5 mm  
**101-05-1**



Socket 1/4" Hex 5.5 mm  
**101-055-1**



Socket 1/4" Hex 6 mm  
**101-06-1**



Socket 1/4" Hex 7 mm  
**101-07-1**



Socket 1/4" Hex 8 mm  
**101-08-1**



Socket 1/4" Hex 9 mm  
**101-09-1**



Socket 1/4" Hex 10 mm  
**101-10-1**



Socket 1/4" Hex 11 mm  
**101-11-1**



Socket 1/4" Hex 12 mm  
**101-12-1**



Socket 1/4" Hex 13 mm  
101-13-1



Extension 1/4" 50 mm  
105-22-1



Extension 1/4" 100 mm  
105-24-1



Universal Joint 1/4"  
105-40-1



Sliding T-Handle 1/4"  
105-42-1



Bit Holder Square 1/4" with Hex 1/4"  
105-48-1



Spinner Handle 1/4"  
105-50-1



Ratchet 1/4" Pear Type, 72 Teeth,  
150 mm  
105-70-1



1/4" Bit Hex 3, 25 mm, Box 5 Pcs  
475-H3-1



1/4" Bit Hex 4, 25 mm, Box 5 Pcs  
475-H4-1



1/4" Bit Hex 5, 25 mm, Box 5 Pcs  
475-H5-1



1/4" Bit Hex 6, 25 mm, Box 5 Pcs  
475-H6-1



1/4" Bit PH1, 25 mm, Box 10 Pcs  
475-PH1-1



1/4" Bit PH2, 25 mm, Box 10 Pcs  
475-PH2-1



1/4" Bit PH3, 25 mm, Box 10 Pcs  
475-PH3-1



1/4" Bit PZ1, 25 mm, Box 10 Pcs  
475-PZ1-1



1/4" Bit PZ2, 25 mm, Box 10 Pcs  
475-PZ2-1



1/4" Bit PZ3, 25 mm, Box 10 Pcs  
475-PZ3-1



1/4" Bit Slotted 4.0, 25 mm, Box 10  
Pcs  
475-4-1



1/4" Bit Slotted 6, 25 mm, Box 10 Pcs  
475-6.0-1