



Cut protection

# KRYTECH 693

Moderate risk - ISO C



CUT PROTECTION  
**LEVEL C**

EN388



4X42C

CATEGORY 2



ISO 13997:

14.5 N

DEXTERITY

EN ISO 21420:  
5/5



Comfort, suppleness and high dexterity thanks to its 18 gauge.  
Touchscreen ability.

Cut level c

Glove with a good visibility for a better user protection

## SPECIFIC ADVANTAGES



### Cut protection

- Cut level easy to identify thanks to the marking on the back of the glove



### Durability

- Glove lifetime extended and reinforced security thanks to the crotch reinforcement between thumb and index that protects the glove from any early damage in this very exposed area



### Skin protection

- Free of harmful substances: DMF Free



### Suitable for touchscreen

- Can be used with touch devices & touch screen



### Guaranteed quality

- Silicone free to prevent traces or defects prior to painting
- Silicone free to prevent traces, defects on metal sheet and glass



### Washability

- Washable 1 time at 40°C

## INDUSTRIES

- Automotive/mechanical industry
- Food industry
- Construction Industry (Carpenters/Joiners)
- Construction Industry (Roofers/Tilers/Glazers)
- Construction Industry (Heating engineers/Plumbers)
- Other industries
- Transport, logistics
- Paper industry

## APPLICATIONS

- Installing steel structures
- Assembly
- Screwing
- Laying tiles, inserts, frames or zinc sheeting
- Handling metal parts
- Packaging
- Warehousing and receipt of goods
- Operating handling equipment
- Order preparation
- Assembly of small parts



Cut protection

# KRYTECH 693

Moderate risk - ISO C


## LEGENDS

EN388

MECHANICAL HAZARDS



PERFORMANCE LEVELS (X = NOT TESTED)



FOOD CONTACT

French decree of 05/08/2020

## PRODUCT DETAILS

Interior finish	Seamless textile support
Gauge	18
Exterior finish	Smooth
Material	Foam nitrile
Cuff characteristic	Knitted Cuff
Colour.s	Yellow
European sizes	6 7 8 9 10 11

## LOGISTIC DETAILS

Packaging	1 pair/bag 12 pairs/bag 48 pairs/carton
-----------	---

## LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/03/22/0590 Ext 01/04/22
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE