

Mechanical tools

For mounting and dismounting bearings



Mounting



SKF Bearing Fitting Tool Kit TMFT series

Helps prevent premature bearing failures

- The TMFT 36 facilitates the mounting of different bearings with bore diameters from 10–55 mm
- The TMFT 24 facilitates the mounting of different bearings with bore diameters from 15–45 mm
- Facilitates correct mounting on shaft, housing and blind applications
- The diameter of the impact ring precisely fits the inner and outer diameter of the bearing
- Impact rings and sleeves are made of high impact resistant material for longevity



Spanners and sockets



SKF Hook Spanners HN series

Exact spanner radius reduces the risk of nut damage



SKF Adjustable Hook Spanners HNA series

Four sizes for tightening or loosening up to 24 nut sizes



SKF Hook Spanners HN ../SNL series

Easy and quick bearing mounting and dismantling in SNL housings



SKF Bearing Lock Nut Spanner TMHN 7 series

For achieving the correct radial clearance




SKF Impact Spanners TMFN series

High impact forces without nut damage



SKF Axial Lock Nut Sockets TMFS series

Easy mounting and dismantling without nut damage



Mounting



Dismounting



Dismounting

SKF Combi Kit TMMK series

Multi-purpose kits for quick and easy mounting and dismantling

Dismounting



SKF EasyPull – TMMA series

Equipped with spring-operated arms and a solid design, the patented SKF EasyPull is one of the most user-friendly and safe tools on the market



SKF Standard Jaw Pullers TMMP series

Versatile two and three arm mechanical pullers



The SKF Reversible Jaw Pullers can also be supplied as three different sets, complete with a workshop stand.



SKF Reversible Jaw Puller TMMR F series

Combined internal and external puller



SKF Heavy Duty Jaw Pullers TMMP & TMHP series

High forces can be easily applied as the puller is self-centring

Hydraulic and strong back pullers




SKF Hydraulic Jaw Puller Kit TMHP 10E

Effortless bearing dismounting up to 100 kN



SKF Hydraulic Puller Kit TMHC 110E

Powerful combination of a jaw and strong back puller



SKF Strong Back Pullers TMBS E series

Easy bearing dismounting even in the tightest spaces

Internal pullers

SKF Internal Bearing Puller Kits TMIP series

Fast and easy bearing dismounting from housings



SKF Blind housing pullers

SKF Deep Groove Ball Bearing Puller Kit TMMD 100

Easy dismounting of bearings in blind housings

SKF Blind Housing Puller Kit TMBP 20E

Removes bearing without dismantling machinery



Accessories



SKF Tri-section Pulling Plates TMMS series

Efficient and correct dismounting

Advanced Hydraulic Spindles TMHS 75 and TMHS 100

Effortless withdrawal force generation



SKF Puller Protection Blankets TMMX series

For additional user safety during dismounting

® SKF is a registered trademark of the SKF Group.

© SKF Group 2015

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB MP/P2 13090 EN · August 2015

