

# Product datasheet

Specifications



bottom support, Altivar process  
Modular, for reduced height power  
module, cabinet integration SF/TS8,  
IP54/UL type 12

VW3A99ACA06

EAN Code: 3606481679789

## Main

|                                       |                           |
|---------------------------------------|---------------------------|
| Range of product                      | Altivar Process Modular   |
| Accessory / separate part category    | Installation accessory    |
| Accessory / separate part type        | Support                   |
| Product compatibility                 | Power module APM          |
| Accessory / separate part destination | Single drive architecture |
| Height                                | 370.0 mm                  |
| Width                                 | 330.0 mm                  |
| Depth                                 | 680.0 mm                  |

## Complementary

|                      |                         |
|----------------------|-------------------------|
| Degree of protection | UL type 12              |
| Device application   | Integration of 1cabinet |
| Kit composition      | 1 bottom support        |
| Product weight       | 6.0 kg                  |

## Environment

|                         |      |
|-------------------------|------|
| IP degree of protection | IP54 |
|-------------------------|------|

## Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Height             | 39.000 cm  |
| Package 1 Width              | 34.000 cm  |
| Package 1 Length             | 70.000 cm  |
| Package 1 Weight             | 8.166 kg   |
| Unit Type of Package 2       | P12        |
| Number of Units in Package 2 | 9          |
| Package 2 Height             | 138.000 cm |
| Package 2 Width              | 80.000 cm  |
| Package 2 Length             | 120.000 cm |
| Package 2 Weight             | 86.494 kg  |

Rates duty January 2016

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 18 |
|----------------------|----|



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Use Better

| Materials and Substances               |                                                                             |
|----------------------------------------|-----------------------------------------------------------------------------|
| Packaging made with recycled cardboard | Yes                                                                         |
| Packaging without single use plastic   | No                                                                          |
| EU RoHS Directive                      | <a href="#">Compliant</a>                                                   |
| REACH Regulation                       | <a href="#">Free of Substances of Very High Concern above the threshold</a> |

### Use Longer

| Lifetime extension |    |
|--------------------|----|
| Repair             | No |

### Use Again

| Repack and remanufacture |     |
|--------------------------|-----|
| Take-back                | Yes |