# Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



# SELECTOR SWITCH 600VAC 10A 30MM SK

9001SKS43BH13

EAN Code: 3389118036147

# Main

Range of product	Harmony 9001SK	
Product or component type	Selector switch	
Device short name	9001SK	
Type of operator	stay put	
Operator profile	Black standard knob	

# Complementary

Bezel material	Plastic	
Mounting diameter	30 mm	
Operator position information	3 positions	
Contacts type and composition	1 C/O	
Product compatibility	9001KA1, mounted side 1 or 2	
Device presentation	Complete product	
Cap/operator or lens colour	Black	
Operator profile	Standard handle	
Type of operator	Stay put	
Size	30 mm	
Cam profile	3	

# **Environment**

Protective treatment	TC	
Ambient air temperature for storage	-4070 °C	
Ambient air temperature for operation	-2570 °C	
Electrical shock protection class	Class II conforming to IEC 61140	
IP degree of protection	IP66 conforming to IEC 60529	
NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13	
Product certifications	UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 CE	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	4.826 cm	
Package 1 Width	5.588 cm	
Package 1 Length	9.398 cm	
Package 1 Weight	86.183 a	

# **Logistical informations**

Country of origin FR

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

### Environmental Data explained >

How we assess product sustainability

Environmental for	otorint

Environmental Disclosure

Product Environmental Profile

### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Offer Marketing Illustration

### Product benefits / Features

# **Technical Benefits**

### Harmony 9001SK



Offer Marketing Illustration

### **Product benefits / Features**



Image of product / Alternate images

### **Alternative**







