

SEALING PLUG 35X35 RD - Sealing plug



1421865

<https://www.phoenixcontact.com/in/products/1421865>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sealing plug, color: red



Commercial data

Item number	1421865
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF7
Product key	AF7DZX
Catalog page	Page 707 (C-2-2019)
GTIN	4055626287652
Weight per piece (including packing)	15.05 g
Weight per piece (excluding packing)	14.28 g
Customs tariff number	39235090
Country of origin	DE

SEALING PLUG 35X35 RD - Sealing plug



1421865


<https://www.phoenixcontact.com/in/products/1421865>

Technical data

Product properties

Product type	Sealing plugs
--------------	---------------

Dimensions

Dimensional drawing	
Length	35 mm
Diameter	34 mm

Material specifications

Material	PA
----------	----

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 100 °C
---------------------------------	-------------------

Mounting

Assembly note	The head of the sealing plug must still be visible after mounting in the screw connection (see "after mounting" photo).
---------------	---

SEALING PLUG 35X35 RD - Sealing plug


1421865

<https://www.phoenixcontact.com/in/products/1421865>



Drawings

Dimensional drawing



Dimensional drawing

SEALING PLUG 35X35 RD - Sealing plug



1421865

<https://www.phoenixcontact.com/in/products/1421865>

Classifications

ECLASS

ECLASS-11.0	27144433
ECLASS-13.0	23111190

ETIM

ETIM 9.0	EC000032
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

SEALING PLUG 35X35 RD - Sealing plug



1421865

<https://www.phoenixcontact.com/in/products/1421865>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in