

PRODUCT-DETAILS

M2SSK1-101

M2SSK1-101 Selector Switch



General Information

Extended Product Type	M2SSK1-101
Product ID	1SFA611280R1001
EAN	7320500304242
Catalog Description	M2SSK1-101 Selector Switch
Long Description	<p>The M2SSK1-101 Selector Switch is: 3-position - Maintained/Momentary - Key - Black/Key - Non-illuminated - Black Plastic - No contact block</p> <p>This Selector Switch is part of ABB's modular plastic range, the most versatile range with a high level of flexibility and market-leading electrical ratings. Engineered for total reliability, longer lifetime, and highest mechanical durability. Self-cleaning contacts ensure reliable operation without the need for maintenance, increasing uptime. A high degree of protection guarantees reliability in extreme environments. The innovative design simplifies the entire process, from selection to easy and quick, tool-free installation. The perfect solution for every application.</p>

Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	8536501999

Popular Downloads

Data Sheet, Technical Information	1SFC151007C02_
Instructions and Manuals	1SFC151011M0201

Dimensions

Product Net Width	0.048 m
Product Net Height	0.03 m
Product Net Depth / Length	0.063 m
Product Net Weight	0.069 kg

Technical

Ambient Air Temperature	Operation -25 ... +70 °C Storage -40 ... +85 °C
Color	Black/Key
Actuator Type	Key
Bezel Material	Black Plastic
Illumination	Non-illuminated
Function	Maintained
Sub-Function	3-position
Maintained Positions	B, C
Key Removal Positions	Both Positions
Key Code	Ronis 455, Key code 71
Degree of Protection	Front IP66
Enclosure Type NEMA	Type1 Type12 Type3R Type4 Type4X
Mechanical Durability	0.5 million

Environmental

RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Date	0635 4
RoHS Information	2CMT2015-005452
WEEE Category	Product Not in WEEE Scope
WEEE B2C / B2B	Business To Business

Certificates and Declarations (Document Number)

cULus Certificate	9AKK107046A9925
Declaration of Conformity - CE	2CMT2015-005452
DNV GL Certificate	E-14107
Environmental Information	1SAC200073H0001
Instructions and Manuals	1SFC151011M0201
RoHS Information	2CMT2015-005452

Container Information

Package Level 1 Units	bag 1 piece
Package Level 1 Width	0.11 m
Package Level 1 Depth / Length	0.15 m
Package Level 1 Height	0.03 m
Package Level 1 Gross	0.069 kg

Weight

Package Level 1 EAN	7320500304242
---------------------	---------------

Classifications

Object Classification Code	S
ETIM 6	EC000222 - Front element for selector switch
ETIM 7	EC000222 - Front element for selector switch
ETIM 8	EC000222 - Front element for selector switch
eClass	V11.0 : 27371213
UNSPSC	39121500
E-Number (Finland)	2338421
E-Number (Norway)	4372540
E-Number (Sweden)	3715600

Categories

Low Voltage Products and Systems → Control Products → Pilot Devices → Modular Plastic Range

