



<b>EAN:</b>	4013288214225	<b>Size:</b>	286x202x55 mm
<b>Part number:</b>	05008901001	<b>Weight:</b>	670 g
<b>Article number:</b>	300/7 Mix 2	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82054000

- Short compact Stubby screwdriver for working in confined spaces
- Lasertip screwdriver with long blade
- Ergonomic 2-component Kraftform handle for precise work
- Hexagonal anti-roll feature against rolling away
- Take it easy tool finder: colour coding according to profile and size

Application-specific mixture of workshop screwdrivers with normal long blade and especially small Stubby screwdrivers with short blade for hard to reach areas. The 2-component Kraftform handle with its practical combination of hard and soft zones allows for a firm grip and precise working. The blades have all the benefits of Wera Bit technology. Special surface treatment of the blades for high corrosion protection and an optimum fit in the screw head. The hexagonal roller guard prevents annoying rolling away of bits in the workplace.






#### Web link

[https://products.wera.de/en/screwdrivers\\_kraftform\\_plus\\_series\\_300\\_300\\_7\\_mix\\_2.html](https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_300_7_mix_2.html)

Wera - 300/7 Mix 2  
05008901001 - 4013288214225

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

Set contents:

	<b>Rack</b>	05134001001 1 x 190 x 50 mm		<b>355 PZ Stubby</b>	05008853001 1 x PZ 1 x 25 mm 05008854001 1 x PZ 2 x 25 mm
	<b>355 PZ</b>	05009310001 1 x PZ 1 x 80 mm 05009317001 1 x PZ 2 x 200 mm		<b>334</b>	05110010001 1 x 1,2 x 6,5 x 150 mm
	<b>335</b>	05110001001 <sup>1)</sup> 1 x 0,5 x 3 x 80 mm 05110007001 1 x 1 x 5,5 x 125 mm <small>1) without Lasertip</small>			

Compact shape




With its compact handle shape and the short blade, the Kraftform Stubbies are particularly suitable for working in confined screwdriving situations.

Tangible ergonomics




The 2-component Kraftform handle allows high power transmission due to the non-slip, softer grip areas and high working speeds due to the hard grip areas, which allow a quick hand switch.

Long life



The special surface treatment of the blades sees to a high level of corrosion protection and optimum fitting accuracy of the screw.

Lasertip prevents slipping out



It happens time and time again that the tip slips out of the screw head when screwdriving, sometimes damaging valuable surfaces or even causing injury. The tips of the Wera Lasertip screwdrivers are microscopically roughened by means of a laser. This rough surface literally "bites" itself firmly into the screw head. Slipping out becomes a thing of the past.


Web link

[https://products.wera.de/en/screwdrivers\\_kraftform\\_plus\\_series\\_300\\_300\\_7\\_mix\\_2.html](https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_300_7_mix_2.html)

Wera - 300/7 Mix 2  
05008901001 - 4013288214225


Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

“Take it easy” Tool Finder




Screwdrivers with “Take it easy” tool finder: colour coding according to profile and size stamp.

Non-roll feature



The hexagonal non-roll feature prevents any rolling away at the workplace.

With useful plastic rack



Including useful rack for well-arranged storage of the screwdrivers.

Web link

[https://products.wera.de/en/screwdrivers\\_kraftform\\_plus\\_series\\_300\\_300\\_7\\_mix\\_2.html](https://products.wera.de/en/screwdrivers_kraftform_plus_series_300_300_7_mix_2.html)

Wera - 300/7 Mix 2  
05008901001 - 4013288214225

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)