

HC-B-BF - Panel-mount flange

1604641

<https://www.phoenixcontact.com/gb/products/1604641>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Panel mounting flange for HEAVYCON ADVANCE TMB housing with bayonet locking



Commercial data

Item number	1604641
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	AF7AAZ
Product key	AF7AAZ
Catalog page	Page 564 (PC-2011)
GTIN	4017918947811
Weight per piece (including packing)	27.855 g
Weight per piece (excluding packing)	10 g
Customs tariff number	85389099
Country of origin	CN

HC-B-BF - Panel-mount flange

1604641

<https://www.phoenixcontact.com/gb/products/1604641>



Technical data


Notes

General	2 for every connector
---------	-----------------------

Product properties

Product type	Panel-mount flange
Pg screw connection	none

Dimensions

Dimensional drawing	
Hole diameter	4.5 mm

Material specifications

Material	Die-cast zinc
----------	---------------

Mechanical properties

Mechanical data

Locking type	Nut
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mounting

Assembly note	In order to guarantee that the protective conductor contact functions even when plugged in at an angle, the two panel-mount flanges must have sufficient electrical contact with the metal mounting panel.
---------------	--

HC-B-BF - Panel-mount flange


1604641

<https://www.phoenixcontact.com/gb/products/1604641>



Drawings

Dimensional drawing



Dimensional drawing

HC-B-BF - Panel-mount flange

1604641

<https://www.phoenixcontact.com/gb/products/1604641>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1604641>



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-B-BF - Panel-mount flange



1604641

<https://www.phoenixcontact.com/gb/products/1604641>

Classifications

ECLASS

ECLASS-13.0	27440192
-------------	----------

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-B-BF - Panel-mount flange



1604641

<https://www.phoenixcontact.com/gb/products/1604641>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk