



129-101-4

1/4"-1/2" Hex Socket Set Metric,
101 Pcs






PRODUCT DETAILS

- 101 piece socket set
- Hex sockets, metric sizes
- Chrome vanadium alloy steel
- Chrome plated bright finish
- High density polyethylene box
- Box with metal latches
- Standards: DIN 3120, DIN 3124, DIN 3122



PRODUCT ATTRIBUTES

Product			
129-101-4	101	80 x 280 x 380 mm	7000 g

SET CONTENT



Hex Key Nickel Plated 1.5 mm
040001



Hex Key Nickel Plated 2 mm - 5/64"
040011



Hex Key Nickel Plated 2.5 mm
040021



Socket 1/4" Hex 4 mm
101-04-1



Socket 1/4" Hex 4.5 mm
101-045-1



Socket 1/4" Hex 5 mm
101-05-1



Socket 1/4" Hex 5.5 mm
101-055-1



Socket 1/4" Hex 6 mm
101-06-1



Socket 1/4" Hex 7 mm
101-07-1



Socket 1/4" Hex 8 mm
101-08-1



Socket 1/4" Hex 9 mm
101-09-1



Socket 1/4" Hex 10 mm
101-10-1



Socket 1/4" Hex 11 mm
101-11-1



Socket 1/4" Hex 12 mm
101-12-1



Socket 1/4" Hex 13 mm
101-13-1



Socket 1/4" Hex 14 mm
101-14-1



Socket 1/4" Deep Hex 6 mm
103-06-1



Socket 1/4" Deep Hex 7 mm
103-07-1



Socket 1/4" Deep Hex 8 mm
103-08-1



Socket 1/4" Deep Hex 10 mm
103-10-1



Socket 1/4" Deep Hex 11 mm
103-11-1



Socket 1/4" Deep Hex 12 mm
103-12-1



Socket 1/4" Deep Hex 13 mm
103-13-1



Socket 1/4" Deep Hex 14 mm
103-14-1



Extension 1/4" 50 mm
105-22-1



Extension 1/4" 100 mm
105-24-1



Extension Flexible 1/4" 140 mm
105-28-1



Universal Joint 1/4"
105-40-1



Sliding T-Handle 1/4"
105-42-1



Bit Holder Square 1/4" with Hex 1/4"
105-48-1



Spinner Handle 1/4"
105-50-1



Ratchet 1/4" Pear Type, 72 Teeth,
150 mm
105-70-1



Hex Bit Socket 1/4" 3 mm
107-H3-1



Hex Bit Socket 1/4" 4 mm
107-H4-1



Hex Bit Socket 1/4" 5 mm
107-H5-1



Hex Bit Socket 1/4" 6 mm
107-H6-1



Phillips Bit Socket 1/4" PH1
107-PH1-1



Phillips Bit Socket 1/4" PH2
107-PH2-1



Pozidriv Bit Socket 1/4" PZ1
107-PZ1-1



Pozidriv Bit Socket 1/4" PZ2
107-PZ2-1



Torx Bit Socket 1/4" T8
107-T08-1



Torx Bit Socket 1/4" T10
107-T10-1



Torx Bit Socket 1/4" T15
107-T15-1



Torx Bit Socket 1/4" T20
107-T20-1



Torx Bit Socket 1/4" T25
107-T25-1



Torx Bit Socket 1/4" T30
107-T30-1



Slotted Bit Socket 1/4" 0.8x4
107-0840-1



Slotted Bit Socket 1/4" 1x5.5
107-1055-1



Slotted Bit Socket 1/4" 1.2x8
107-1280-1



Socket 1/2" Deep Bihex 13 mm
124-13-1



Socket 1/2" Deep Bihex 17 mm
124-17-1



Socket 1/2" Deep Bihex 19 mm
124-19-1



Socket 1/2" Deep Bihex 22 mm
124-22-1



Extension 1/2" 125 mm
125-23-1



Extension 1/2" 250 mm
125-25-1



Universal Joint 1/2"
125-40-1



Sliding T-Handle Head 1/2"
125-43-1



Bit Holder 1/2" to Hex 5/16"
125-48-1



Ratchet 1/2" Pear Type, 72 Teeth,
250 mm
125-70-1



5/16" Bit Hex 10, 2 Pcs
470-H10-1



5/16" Bit Hex 6, 2 Pcs
470-H6-1



5/16" Bit Hex 7, 2 Pcs
470-H7-1



5/16" Bit Hex 8, 2 Pcs
470-H8-1



5/16" Bit Torx 30, 2 Pcs
470-T30-1



5/16" Bit Torx 40, 2 Pcs
470-T40-1



5/16" Bit Torx 45, 2 Pcs
470-T45-1



5/16" Bit Torx 50, 2 Pcs
470-T50-1



5/16" Bit Torx 55, 2 Pcs
470-T55-1



5/16" Bit Slotted 10, 2 Pcs
470-10.0-1



5/16" Bit Slotted 12, 2 Pcs
470-12.0-1



5/16" Bit Slotted 8.0, 2 Pcs
470-8.0-1



1/4" Bit Hex 3, 25 mm, Box 5 Pcs
475-H3-1



1/4" Bit Hex 4, 25 mm, Box 5 Pcs
475-H4-1



1/4" Bit Hex 5, 25 mm, Box 5 Pcs
475-H5-1



1/4" Bit T10, 25 mm, Box 10 Pcs
475-T10-1



1/4" Bit T15, 25 mm, Box 10 Pcs
475-T15-1



1/4" Bit T20, 25 mm, Box 10 Pcs
475-T20-1



1/4" Bit T25, 25 mm, Box 10 Pcs
475-T25-1



1/4" Bit T27, 25 mm, Box 10 Pcs
475-T27-1



1/4" Bit T30, 25 mm, Box 5 Pcs
475-T30-1



Socket 1/2" Hex 8 mm
121-08-1



Socket 1/2" Hex 10 mm
121-10-1



Socket 1/2" Hex 12 mm
121-12-1



Socket 1/2" Hex 13 mm
121-13-1



Socket 1/2" Hex 14 mm
121-14-1



Socket 1/2" Hex 16 mm
121-16-1



Socket 1/2" Hex 17 mm
121-17-1



Socket 1/2" Hex 19 mm
121-19-1



Socket 1/2" Hex 20 mm
121-20-1



Socket 1/2" Hex 21 mm
121-21-1



Socket 1/2" Hex 22 mm
121-22-1



Socket 1/2" Hex 23 mm
121-23-1



Socket 1/2" Hex 24 mm
121-24-1



Socket 1/2" Hex 26 mm
121-26-1



Socket 1/2" Hex 27 mm
121-27-1



Socket 1/2" Hex 28 mm
121-28-1



Socket 1/2" Hex 30 mm
121-30-1



Socket 1/2" Hex 32 mm
121-32-1