

C-SCF 2,5/4,8X0,5 - Connector

3240157

<https://www.phoenixcontact.com/gb/products/3240157>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Slip-on sleeve, non-insulated, 1.5 ... 2.5 mm², 4.8 x 0.5

Your advantages

- They round out the product range in terms of connectors
- The uninsulated slip-on sleeves and flat plugs are made from electrolytically tin-plated brass

Commercial data

Item number	3240157
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BH3452
Product key	BH3452
Catalog page	Page 498 (C-3-2019)
GTIN	4046356453745
Weight per piece (including packing)	0.47 g
Weight per piece (excluding packing)	0.47 g
Customs tariff number	85366990
Country of origin	BE

C-SCF 2,5/4,8X0,5 - Connector

3240157

<https://www.phoenixcontact.com/gb/products/3240157>




Technical data

Product properties

Product type	Connector
Product property	Manufactured according to DIN 46247
	Crimp area with embossing
	Tin-plated

Dimensions

Dimensional drawing	
Width	4.8 mm
Sleeve length	16 mm
Maximum stripping length	8 mm
Min. material thickness	0.4 mm

Material specifications

Color	silver-colored
Material	Brass
Coating	tin-plated
Insulating material	nicht zutreffend
Components	halogen-free

Mechanical properties

Technical data	
Sleeve length	16 mm

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	110 °C

C-SCF 2,5/4,8X0,5 - Connector


3240157

<https://www.phoenixcontact.com/gb/products/3240157>



Drawings

Dimensional drawing



C-SCF 2,5/4,8X0,5 - Connector



3240157

<https://www.phoenixcontact.com/gb/products/3240157>

Classifications

ECLASS

ECLASS-13.0	27400212
-------------	----------

ETIM

ETIM 9.0	EC001059
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

C-SCF 2,5/4,8X0,5 - Connector

3240157

<https://www.phoenixcontact.com/gb/products/3240157>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk