

Professionally approved products.

Datasheet

RS Jigsaw Blades

Professional jigsaw blades for use in power tools. Blades available for the clean high speed cutting of wood, metal and ceramics.

- Application marked on the side of the blade
- High Speed Steel blades for metal cutting (HSS)
- High Carbon Steel blades for wood cutting (HCS)
- Carbide blades for ceramic cutting
- Supplied in packs of 5

Universal Shank Jigsaw Blades



RS [799-9358](#)

5 x 92mm 10TPI HCS Wood Cutting Blade



RS [799-9360](#)

5 x 70mm 12TPI HSS Metal Cutting Blade

Professionally approved products.



RS [799-9376](#)

5 x 70mm 21TPI HSS Metal Cutting Blade



RS [799-9389](#)

5 x 92mm 8TPI HSS Metal Cutting Blade

T-shank Jigsaw Blades



RS [799-9351](#) (T111C)

5 x 100mm 8TPI HCS Wood Cutting Blade



RS [799-9370](#) (T144D)

5 x 100mm 6TPI HCS Wood Cutting Blade

Professionally approved products.



RS [799-9336](#) (T101D)

5 x 100mm 6TPI HCS Wood Cutting Blade



RS [799-9345](#) (T101B)

5 x 100mm 10TPI HCS Wood Cutting Blade



RS [799-9320](#) (T118A)

5 x 75mm 21TPI HSS Metal Cutting Blade



RS [799-9342](#) (T127D)

5 x 100mm 8TPI HSS Metal Cutting Blade

Professionally approved products.



RS [799-9367](#) (T101A)

5 x 100mm 14TPI HCS Metal Cutting Blade



RS [799-9339](#)

5 x 75mm 21TPI Bi-Metal Metal Cutting Blade



RS [799-9386](#)

5 x 100mm 12TPI Bi-Metal Metal Cutting Blade



RS [799-9332](#) (T345XF)

5 x 132mm 5-10TPI Bi-Metal Wood & Metal Cutting Blade

Professionally approved products.



RS [799-9395](#)

5 x 75mm 50 Grit Carbide Ceramic Cutting Blade



RS [799-9392](#)

5 x 75mm 30 Grit Carbide Ceramic Cutting Blade

Makita Compatible Shank Jigsaw Blades



RS [799-9398](#)

5 x 80mm 12TPI HCS Wood Cutting Blade



RS [799-9364](#)

5 x 75mm 21TPI HSS Metal Cutting Blade

Professionally approved products.



RS [799-9382](#)

5 x 75mm 8TPI HSS Metal Cutting Blade