

Crimping pliers - CRIMPFOX 6H - 1212046

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.14 mm² ... 6 mm², unlockable pressure lock, lateral entry

Your advantages

- ✔ These compact crimping pliers have been designed to reduce effort when working
- ✔ The way in which the handles and the die are arranged means that the ferrules can be fitted however the tool is held



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 455749
GTIN	4046356455749
Weight per Piece (excluding packing)	445.800 g
Custom tariff number	82032000
Country of origin	Germany

Technical data

Dimensions

Length (b)	175 mm
------------	--------

General

Color	black
Compression	HEX crimp
Type of contact	Insulated and uninsulated ferrules
Designation	Crimping position 1
Min. cross section	0.14 mm ²
Max. cross section	6 mm ²
AWG min	25
AWG max	10

Crimping pliers - CRIMPFOX 6H - 1212046

Technical data

General

Weight	380 g
Min. cross section	0.14 mm ²
Max. cross section	6 mm ²
AWG min	25
AWG max	10

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040300
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Approvals

Approvals

Crimping pliers - CRIMPFOX 6H - 1212046


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU x- DE.xx08.B.02974
-----	---	--------------------------

Accessories

Accessories

Mounting material

Replacement spring - CRIMPFOX/SPR-2 - 1212047



Spare recuperating spring
