


STANDARD SDS-PLUS



2 cutter SDS plus drill bits suitable for masonry and concrete. The solid carbide tip with centering point and optimised flutes offers fast drilling speeds in a contractors, low cost option.



Part No.	D mm	L1 mm	L2 mm	Pack
D-00016	4	110	50	1
D-00022	5	110	50	1
D-00038	5	160	100	1
D-00044	5.5	110	50	1
D-16106	5.5	160	100	1
D-00050	6	110	50	1
D-00066	6	160	100	1
D-00072	6	210	150	1
D-00088	6.5	110	50	1
D-00094	6.5	160	100	1
D-00103	7	110	50	1
D-00119	7	160	100	1
D-00125	8	110	50	1
D-00131	8	160	100	1
D-00147	8	210	150	1
D-00153	8	260	200	1
D-08056	9	160	100	1
D-00175	10	160	100	1
D-00181	10	210	150	1
D-00197	10	260	200	1
D-00212	11	160	100	1
D-00228	12	160	100	1
D-00234	12	210	150	1
D-00240	12	260	200	1
D-14102	12.5	160	100	1
D-00256	13	160	100	1
D-00262	14	160	100	1
D-00278	14	260	200	1
D-00284	15	160	100	1
D-17550	15	460	400	1
D-03981	16	160	100	1
D-00290	16	210	150	1
D-16156	16	260	200	1
D-00309	16	310	250	1
D-16287	16	460	400	1
D-00315	17	210	150	1
D-00321	18	210	150	1
D-00337	18	300	250	1
D-17566	18	460	400	1
D-00343	19	210	150	1
D-16293	19	460	400	1
D-00359	20	210	150	1
D-00365	20	310	250	1
D-15235	20	460	400	1
D-00371	22	260	200	1
D-15241	22	460	400	1
D-16302	24	460	400	1
D-00387	25	260	200	1
D-15257	25	460	400	1
D-00393	26	260	200	1
D-15263	26	460	400	1
D-16318	28	460	400	1
D-17572	30	460	400	1

MULTI PACK STANDARD SDS-PLUS



D-03888



D-44987



5PC SET				
D-03888	5.5	110		5
	7	110		
	6	160		
	7	160		
	8	160		
D-44987	5.8	110		5
	6.5	110		
	6.5	60		
	9.5	160		
	12.7	160		
25PC PACKS				
D-01155-25	5	110	50	25
D-03763-25	5.5	110	50	25
D-03779-25	5.5	160	100	25
D-01161-25	6	110	50	25
D-01177-25	6	160	100	25
D-03785-25	6.5	110	50	25
D-03791-25	6.5	160	100	25
D-03800-25	7	110	50	25
D-03816-25	7	160	100	25
D-01183-25	8	160	100	25
D-01199-25	8	210	150	25
D-01208-25	10	160	100	25
D-03707-25	10	210	150	25
D-03713-25	12	160	100	25
D-03729-25	12	210	150	25