

Comfortable medium-duty PVC gloves, for comfortable hand protection even at low temperatures

- **Added comfort:** Underneath their soft PVC coating, AlphaTec® 23-200 safety gloves feature a 13-gauge knitted cotton liner, combining excellent comfort with moderate mechanical and chemical protection
- **Enhanced grip:** Their dipped rough sandblast finish makes for better grip performance, even in wet conditions, for more confident handling and secure personal protection
- **Food handling compliance:** Suitable for various food processing applications, AlphaTec® 23-200 work gloves adhere to relevant FDA and EU food handling regulations

Industries

- Food Processing
- Food Service
- Chemical
- Janitorial / Sanitation

Applications

- Defeathering and skinning
- Primary cutting
- Deboning
- Chemical Handling
- Janitorial use



Previously known as: VersaTouch® 23-200

Key Features

- **13-gauge knitted cotton liner:** For truly comfortable hand protection
- **Rough sandblast finish:** Excellent grip, even in wet conditions
- **FDA and EU food handling compliance:** Ideal food safety gloves



Performance Standards

ANSI/ISEA 105-2024



0493

EN388: 2016



3121B

EN ISO 374-1:2016



KLT

EN ISO 374-5:2016



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 23-200	Coating Material: PVC	7, 8, 9, 10	300 / 11.8	Blue	• 12 pairs per bag, 6 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.