Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Cable tie, Thorsman installation material, 160x2.5mm, clear

IMT46407

Main

product range	Thorsman	
Range of product	Thorsman installation material	
product type	Cable tie	
colour	Clear	
quantity per package	Set of 100	

Complementary

Minimum tightening diameter	3 mm	
Maximum tightening diameter	39 mm	
Condition of use	Indoor	
resistance to tearing	Resistance to tearing: 80 N	
Material	PA (polyamide) 6.6 UV-stabilised	
Length	160 mm	
Width	2.5 mm	
Thickness	1.1 mm	
Net weight	0.041 kg	
Market segment	Small commercial	

Environment

Environmental characteristic	Fire resistance needle flame 30 s conforming to IEC 60695-11-5	
Flame retardance	Self-extinguishing conforming to UL 94 V2	
Ambient air temperature for operation	-4085 °C	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	9.000 cm
Package 1 Length	19.000 cm
Package 1 Weight	47.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	90

Package 2 Height	10.000 cm
Package 2 Width	38.000 cm
Package 2 Length	50.000 cm
Package 2 Weight	4.252 kg
Unit Type of Package 3	S35
Number of Units in Package 3	180
Package 3 Height	15.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	9.525 kg

Contractual warranty

Warranty 18 mois



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
Halogen content performance	Halogen free product
PVC free	Yes

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No