

# OCS PANEL 1008 PC - Mounting panel



1471785

<https://www.phoenixcontact.com/gb/products/1471785>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting panel for housing size of 10" x 8", material: polycarbonate, color: white



## Your advantages

- Internationally certified housing system
- Special plastic enables safe continuous operation
- Provides protection against the ingress of jet water
- Withstands even heavy mechanical strain

## Commercial data

Item number	1471785
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ACFDBZ
Product key	ACFDBZ
GTIN	4063151881122
Weight per piece (including packing)	0.187 kg
Weight per piece (excluding packing)	0.183 kg
Customs tariff number	39269097
Country of origin	DE

# OCS PANEL 1008 PC - Mounting panel



1471785

<https://www.phoenixcontact.com/gb/products/1471785>

## Technical data

### Product properties

Product type	Mounting plate
Housing type	Outdoor housing
Housing series	OCS
Product family	OCS..1008..

### Dimensions

Width	171 mm
Height	222 mm
Depth	4 mm

### Material specifications

Color	white (RAL 9010)
Material ()	Polycarbonate
Flammability rating according to UL 94	HB
Insulating material	PC
Surface characteristics	untreated

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

### Mounting

Mounting type	Screw mounting
---------------	----------------

### Packaging specifications

Type of packaging	none
-------------------	------

# OCS PANEL 1008 PC - Mounting panel



1471785

<https://www.phoenixcontact.com/gb/products/1471785>

## Classifications

### ECLASS

ECLASS-13.0	27190605
-------------	----------

### ETIM

ETIM 9.0	EC002779
----------	----------

# OCS PANEL 1008 PC - Mounting panel



1471785

<https://www.phoenixcontact.com/gb/products/1471785>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)