


PRODUCT-DETAILS

# IS2-ES2000MF2K

## IS2-ES2000MF2K Control and Automation Board



### General Information

|                       |   |
|-----------------------|---|
| Extended Product Type | IS2-ES2000MF2K  |
| Product ID            | ES2000MF2K  |
| EAN                   | 8015646743640   |
| Catalog Description   | IS2-ES2000MF2K Control and Automation Board                                     |
| Long Description      | Cabinets for compartments 2000x1000x1000mm (HxDxW) with Cable container W=200mm |

### Technical

|                        |  |
|------------------------|--|
| Standards              | IEC 62208, IEC 61439-1-2<br>NEMA 1, 3R, 12 |
| Product Name           | Control and Automation Board               |
| Product Type           | 5B5B10B180                                 |
| Door Type              | Single                                     |
| Surface Finishing      | Orange Peel, RAL 7035                      |
| Door Surface Finishing | Opaque                                     |
| Material               | Sheet Steel Metal                          |
| Remarks                | ETIM                                       |
| RAL Number             | RAL 7035 - Light Grey                      |

### Environmental

|                      |                        |
|----------------------|------------------------|
| Degree of Protection | acc. to IEC 60529 IP65 |
| Environmental        | 1STC804013D0209        |

## Information

**Dimensions**

|                            |             |
|----------------------------|-------------|
| Product Net Width          | 1010 mm     |
| Product Net Height         | 2111.5 mm   |
| Product Net Depth / Length | 1040 mm     |
| Product Net Weight         | 120.8280 kg |

**Container Information**

|                                |               |
|--------------------------------|---------------|
| Package Level 1 Units          | 1 piece       |
| Package Level 1 Width          | 1.000 m       |
| Package Level 1 Height         | 2.000 m       |
| Package Level 1 Depth / Length | 1.000 m       |
| Package Level 1 Gross Weight   | 128.540 kg    |
| Package Level 1 EAN            | 8015646743640 |

**Ordering**

|                         |            |
|-------------------------|------------|
| Minimum Order Quantity  | 1 piece    |
| Customs Tariff Number   | 85381000   |
| Country of Origin       | Italy (IT) |
| Selling Unit of Measure | piece      |

**Certificates and Declarations (Document Number)**

|                                |                 |
|--------------------------------|-----------------|
| Declaration of Conformity - CE | 1STC860113      |
| Environmental Information      | 1STC804013D0209 |
| Instructions and Manuals       | 1STM604121R0006 |
| RoHS Information               | 1STC860065      |

**Popular Downloads**

|                                   |                 |
|-----------------------------------|-----------------|
| Data Sheet, Technical Information | 1STC804013D0209 |
| Instructions and Manuals          | 1STM604121R0006 |

**Classifications**

|                            |   |
|----------------------------|---|
| ETIM 6                     | EC000261 - Enclosure/switchgear cabinet (empty)             |
| ETIM 7                     | EC000261 - Enclosure/switchgear cabinet (empty)             |
| ETIM 8                     | EC000261 - Enclosure/cabinet (empty)                        |
| WEEE Category              | 4. Large Equipment (Any External Dimension More Than 50 cm) |
| WEEE B2C / B2B             | Business To Business  |
| CN8                        | 85381000  |
| Object Classification Code | U   |

---

## Categories

---

Low Voltage Products and Systems → Enclosures → Automation and Control Enclosures (System pro E control) → Enclosures - Baying (Horizontal Joining)

