

A-INL-M32-P-LG - Counter nut

1417662

<https://www.phoenixcontact.com/gb/products/1417662>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads M32 x 1.5, color: light gray



Commercial data

Item number	1417662
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AF7DZX
Product key	AF7DZX
Catalog page	Page 686 (C-2-2019)
GTIN	4055626121659
Weight per piece (including packing)	7.34 g
Weight per piece (excluding packing)	7.6 g
Customs tariff number	39269097
Country of origin	TR

A-INL-M32-P-LG - Counter nut



1417662


<https://www.phoenixcontact.com/gb/products/1417662>

Technical data

Product properties

Product type	Flat nut
Thread type	M32

Dimensions

Dimensional drawing	
Length	7 mm
Diameter	32 mm
Connecting thread diameter	32 mm
Wrench size, counter nut	41 mm
Hexagon angular dimension	46.1 mm
Thread type connection side	M32 x 1.5
Thread pitch	1.5 mm

Material specifications

Material	PA 6.6 GF
----------	-----------

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 100 °C

A-INL-M32-P-LG - Counter nut


1417662

<https://www.phoenixcontact.com/gb/products/1417662>



Drawings

Dimensional drawing



A-INL-M32-P-LG - Counter nut



1417662

<https://www.phoenixcontact.com/gb/products/1417662>

Classifications

ECLASS

ECLASS-13.0	27140807
-------------	----------

ETIM

ETIM 9.0	EC000879
----------	----------

UNSPSC

UNSPSC 21.0	31161700
-------------	----------

A-INL-M32-P-LG - Counter nut



1417662

<https://www.phoenixcontact.com/gb/products/1417662>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk