



Disposable

SOLO 997

Nitrile | Chlorinated

Excellent mechanical resistance, ideal in oily environments

SPECIFIC ADVANTAGES



Comfort

- Excellent dexterity thanks to flexibility and reduced material thickness



Skin protection

- Recommended for oily environments in industry



Practical

- Worn alone or as an outer-glove

INDUSTRIES

- Automotive/mechanical industry
- Laboratory
- Aeronautics industry

APPLICATIONS

- Work with composite materials (resins)
- Manufacturing of medicines
- Pharmaceutical preparation
- Research, analysis, handling of precision parts
- Assembly of small oily parts



CHEMICAL PROTECTION
TYPE B

EN ISO 374-1



TYPE B
JKT

EN ISO 374-5



VIRUS

CATEGORY 3



0334

DEXTERITY

EN ISO 21420:
5/5





Disposable

SOLO 997

Nitrile | Chlorinated

LEGENDS

EN ISO 374-1



TYPE B

CHEMICAL RISKS

J: n-Heptane
K: Sodium hydroxide 40%
T: Formaldehyde 37%

EN ISO 374-5



VIRUS

MICRO-ORGANISMS

Protection against bacteria, fungi and virus



FOOD CONTACT

French decree of 05/08/2020

PRODUCT DETAILS

Interior finish	Chlorinated
Exterior finish	Smooth with pebbled fingertips
Material	Nitrile
Colour.s	Blue
Length (cm)	24
Thickness (mm)	0.10
European sizes	6 7 8 9
AQL Liquidproofness	1.5
Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)	1.7E+11 Ω
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	7.1E+8 Ω

LOGISTIC DETAILS

Packaging	100 gloves/box 1000 gloves/carton
-----------	--------------------------------------

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/02/24/0270
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France