


Cable Assemblies



Jack body shown, dimensions apply to plugs/jacks of various connector styles

BNC Straight Plug / Straight Plug

Body Plating	Centre Contact Plating	Nominal Impedance Ohms	Cable End 1	Cable End 2	Cable	Dim.L (m)	Part No.
Nickel	Gold	50	Straight Plug	Straight Plug	RG58	0.25	1337769-1
Nickel	Gold	50	Straight Plug	Straight Plug	RG58	0.50	1337769-2
Nickel	Gold	50	Straight Plug	Straight Plug	RG58	1.00	1337769-3
Nickel	Gold	50	Straight Plug	Straight Plug	RG58	1.50	1337769-4
Nickel	Gold	50	Straight Plug	Straight Plug	RG58	2.00	1337769-5
Silver	Silver	50	Straight Plug	Straight Plug	RG58	0.50	1337771-2
Silver	Silver	50	Straight Plug	Straight Plug	RG58	0.60	1337771-3
Silver	Silver	50	Straight Plug	Straight Plug	RG58	1.00	1337771-4
Silver	Silver	50	Straight Plug	Straight Plug	RG58	1.20	1337771-5
Silver	Silver	50	Straight Plug	Straight Plug	RG58	1.50	1337771-6
Silver	Silver	50	Straight Plug	Straight Plug	RG58	1.80	1337771-7
Silver	Silver	50	Straight Plug	Straight Plug	RG58	2.00	1337771-8
Nickel	Gold	75	Straight Plug	Straight Plug	RG59	0.25	1337775-1
Nickel	Gold	75	Straight Plug	Straight Plug	RG59	0.50	1337775-2
Nickel	Gold	75	Straight Plug	Straight Plug	RG59	1.00	1337775-3
Nickel	Gold	75	Straight Plug	Straight Plug	RG59	1.50	1337775-4
Silver	Silver	75	Straight Plug	Straight Plug	RG59	0.25	1337777-1
Silver	Silver	75	Straight Plug	Straight Plug	RG59	0.50	1337777-2
Silver	Silver	75	Straight Plug	Straight Plug	RG59	1.00	1337777-3
Silver	Silver	75	Straight Plug	Straight Plug	RG59	1.20	1337777-4
Silver	Silver	75	Straight Plug	Straight Plug	RG59	1.50	1337777-5
Nickel	Gold	75	Straight Plug	Straight Plug	RG62	0.25	1337781-1
Nickel	Gold	75	Straight Plug	Straight Plug	RG62	0.50	1337781-2
Nickel	Gold	75	Straight Plug	Straight Plug	RG62	1.00	1337781-3
Nickel	Gold	75	Straight Plug	Straight Plug	RG62	1.50	1337781-4

Cable Assemblies

BNC Straight Plug / Elbow Plug

Body Plating	Centre Contact Plating	Nominal Impedance Ohms	Cable End 1	Cable End 2	Cable	Dim. L (m)	Part No.
Nickel	Gold	50	Straight Plug	Elbow Plug	RG58	0.25	1337772-1
Nickel	Gold	50	Straight Plug	Elbow Plug	RG58	0.50	1337772-2
Nickel	Gold	50	Straight Plug	Elbow Plug	RG58	1.00	1337772-3
Nickel	Gold	50	Straight Plug	Elbow Plug	RG58	1.50	1337772-4
Nickel	Gold	75	Straight Plug	Elbow Plug	RG59	0.25	1337778-1
Nickel	Gold	75	Straight Plug	Elbow Plug	RG59	0.50	1337778-2
Nickel	Gold	75	Straight Plug	Elbow Plug	RG59	1.00	1337778-3
Nickel	Gold	75	Straight Plug	Elbow Plug	RG59	1.50	1337778-4
Nickel	Gold	75	Straight Plug	Elbow Plug	RG62	0.25	1337782-1
Nickel	Gold	75	Straight Plug	Elbow Plug	RG62	0.50	1337782-2
Nickel	Gold	75	Straight Plug	Elbow Plug	RG62	1.00	1337782-3
Nickel	Gold	75	Straight Plug	Elbow Plug	RG62	1.50	1337782-4

BNC Elbow Plug / Elbow Plug

Body Plating	Centre Contact Plating	Nominal Impedance Ohms	Cable End 1	Cable End 2	Cable	Dim. L (m)	Part No.
Nickel	Gold	50	Elbow Plug	Elbow Plug	RG58	0.25	1337773-1
Nickel	Gold	50	Elbow Plug	Elbow Plug	RG58	0.50	1337773-2
Nickel	Gold	50	Elbow Plug	Elbow Plug	RG58	1.00	1337773-3
Nickel	Gold	50	Elbow Plug	Elbow Plug	RG58	1.50	1337773-4
Nickel	Gold	75	Elbow Plug	Elbow Plug	RG59	0.25	1337779-1
Nickel	Gold	75	Elbow Plug	Elbow Plug	RG59	0.50	1337779-2
Nickel	Gold	75	Elbow Plug	Elbow Plug	RG59	1.00	1337779-3
Nickel	Gold	75	Elbow Plug	Elbow Plug	RG59	1.50	1337779-4
Nickel	Gold	75	Elbow Plug	Elbow Plug	RG62	0.25	1337783-1
Nickel	Gold	75	Elbow Plug	Elbow Plug	RG62	0.50	1337783-2
Nickel	Gold	75	Elbow Plug	Elbow Plug	RG62	1.00	1337783-3
Nickel	Gold	75	Elbow Plug	Elbow Plug	RG62	1.50	1337783-4

Cable Assemblies

BNC Straight Plug / Straight Jack

Body Plating	Centre Contact Plating	Nominal Impedance Ohms	Cable End 1	Cable End 2	Cable	Dim. L (m)	Part No.
Nickel	Gold	50	Straight Plug	Straight Jack	RG58	0.25	1337774-1
Nickel	Gold	50	Straight Plug	Straight Jack	RG58	0.50	1337774-2
Nickel	Gold	50	Straight Plug	Straight Jack	RG58	1.00	1337774-3
Nickel	Gold	50	Straight Plug	Straight Jack	RG58	1.50	1337774-4
Nickel	Gold	75	Straight Plug	Straight Jack	RG59	0.25	1337780-1
Nickel	Gold	75	Straight Plug	Straight Jack	RG59	0.50	1337780-2
Nickel	Gold	75	Straight Plug	Straight Jack	RG59	1.00	1337780-3
Nickel	Gold	75	Straight Plug	Straight Jack	RG59	1.50	1337780-4
Nickel	Gold	75	Straight Plug	Straight Jack	RG62	0.25	1337784-1
Nickel	Gold	75	Straight Plug	Straight Jack	RG62	0.50	1337784-2
Nickel	Gold	75	Straight Plug	Straight Jack	RG62	1.00	1337784-3
Nickel	Gold	75	Straight Plug	Straight Jack	RG62	1.50	1337784-4

TNC Straight Plug / Straight Plug

Body Plating	Centre Contact Plating	Nominal Impedance Ohms	Cable End 1	Cable End 2	Cable	Dim. L (m)	Part No.
Nickel	Gold	50	Straight Plug	Straight Plug	RG174	0.25	1337820-1
Nickel	Gold	50	Straight Plug	Straight Plug	RG174	0.50	1337820-2
Nickel	Gold	50	Straight Plug	Straight Plug	RG174	1.00	1337820-3

N Straight Plug / Straight Plug

Body Plating	Centre Contact Plating	Nominal Impedance Ohms	Cable End 1	Cable End 2	Cable	Dim. L (m)	Part No.
Nickel	Gold	50	Straight Plug	Straight Plug	RG58	0.25	1337801-1
Nickel	Gold	50	Straight Plug	Straight Plug	RG58	0.50	1337801-2
Nickel	Gold	50	Straight Plug	Straight Plug	RG58	1.00	1337801-3
Nickel	Gold	50	Straight Plug	Straight Plug	RG58	1.50	1337801-4
Silver	Silver	50	Straight Plug	Straight Plug	RG50	0.25	1337802-1
Silver	Silver	50	Straight Plug	Straight Plug	RG59	0.50	1337802-2
Silver	Silver	50	Straight Plug	Straight Plug	RG60	1.00	1337802-3
Silver	Silver	50	Straight Plug	Straight Plug	RG61	1.50	1337802-4
Nickel	Gold	50	Straight Plug	Straight Plug	RG213	0.25	1337803-1
Nickel	Gold	50	Straight Plug	Straight Plug	RG213	0.50	1337803-2
Nickel	Gold	50	Straight Plug	Straight Plug	RG213	1.00	1337803-3
Nickel	Gold	50	Straight Plug	Straight Plug	RG213	1.50	1337803-4

Cable Assemblies

UHF Straight Plug / Straight Plug

Body Plating	Centre Contact Plating	Nominal Impedance Ohms	Cable End 1	Cable End 2	Cable	Dim. L (m)	Part No.
Silver	Silver	50	Straight Plug	Straight Plug	RG58	0.25	1337821-1
Silver	Silver	50	Straight Plug	Straight Plug	RG58	0.50	1337821-2
Silver	Silver	50	Straight Plug	Straight Plug	RG58	1.00	1337821-3

SMB Straight Plug / Straight Plug

Body Plating	Centre Contact Plating	Nominal Impedance Ohms	Cable End 1	Cable End 2	Cable	Dim. L (m)	Part No.
Gold	Gold	50	Straight Plug	Straight Plug	RG316	0.25	1337814-1
Gold	Gold	50	Straight Plug	Straight Plug	RG316	0.50	1337814-2
Gold	Gold	50	Straight Plug	Straight Plug	RG316	1.00	1337814-3
Gold	Gold	50	Straight Plug	Straight Plug	RG174	0.25	1337815-1
Gold	Gold	75	Straight Plug	Straight Plug	RG174	0.50	1337815-2
Gold	Gold	75	Straight Plug	Straight Plug	RG174	1.00	1337815-3

SMB Straight Plug / Elbow Plug

Body Plating	Centre Contact Plating	Nominal Impedance Ohms	Cable End 1	Cable End 2	Cable	Dim. L (m)	Part No.
Gold	Gold	50	Straight Plug	Elbow Plug	RG174	0.25	1337816-1
Gold	Gold	50	Straight Plug	Elbow Plug	RG174	0.50	1337816-2
Gold	Gold	50	Straight Plug	Elbow Plug	RG174	1.00	1337816-3

SMB Elbow Plug / Elbow Plug

Body Plating	Centre Contact Plating	Nominal Impedance Ohms	Cable End 1	Cable End 2	Cable	Dim. L (m)	Part No.
Gold	Gold	50	Elbow Plug	Elbow Plug	RG174	0.25	1337817-1
Gold	Gold	50	Elbow Plug	Elbow Plug	RG174	0.50	1337817-2
Gold	Gold	50	Elbow Plug	Elbow Plug	RG174	1.00	1337817-3
Gold	Gold	50	Elbow Plug	Elbow Plug	RG316	0.25	1337818-1
Gold	Gold	50	Elbow Plug	Elbow Plug	RG316	0.50	1337818-2
Gold	Gold	50	Elbow Plug	Elbow Plug	RG316	1.00	1337818-3
Gold	Gold	50	Elbow Plug	Elbow Plug	RG316	2.00	1337818-4
Gold	Gold	50	Elbow Plug	Elbow Plug	RG316	3.00	1337818-5

Cable Assemblies

SMC Straight Plug / Straight Plug

Body Plating	Centre Contact Plating	Nominal Impedance Ohms	Cable End 1	Cable End 2	Cable	Dim. L (m)	Part No.
Gold	Gold	50	Straight Plug	Straight Plug	RG174	0.25	1337819-1
Gold	Gold	50	Straight Plug	Straight Plug	RG174	0.50	1337819-2
Gold	Gold	50	Straight Plug	Straight Plug	RG174	1.00	1337819-3

MCX Straight Plug / Straight Plug

Body Plating	Centre Contact Plating	Nominal Impedance Ohms	Cable End 1	Cable End 2	Cable	Dim. L (m)	Part No.
Nickel	Gold	50	Straight Plug	Straight Plug	RG174	0.25	1337785-1
Nickel	Gold	50	Straight Plug	Straight Plug	RG174	0.50	1337785-2
Nickel	Gold	50	Straight Plug	Straight Plug	RG174	1.00	1337785-3

MCX Straight Plug / Elbow Plug

Body Plating	Centre Contact Plating	Nominal Impedance Ohms	Cable End 1	Cable End 2	Cable	Dim. L (m)	Part No.
Nickel	Gold	50	Straight Plug	Elbow Plug	RG174	0.25	1337786-1
Nickel	Gold	50	Straight Plug	Elbow Plug	RG174	0.50	1337786-2
Nickel	Gold	50	Straight Plug	Elbow Plug	RG174	1.00	1337786-3