



PRODUCT-DETAILS

E 91N/125

Fuse disconnecter



概要信息	
产品型号	E 91N/125
产品ID	2CSM277352R1801
欧洲商品编号(EAN)	8012542771128
目录说明	Fuse disconnector
详细描述	E 90 50/125 fuse holders are appropriate to protect against overloads and short circuits. They are designed for use with cylindrical fuses from 50 to 125 A.

技术参数	
适用于	E 90
适用产品系列	Fuse holders
额定电压 (U _r)	acc. To IEC 690 V acc. To UL 690 V
额定工作电压	AC-20B 690 V
额定绝缘电压 (U _i)	1 kV
额定频率 (f)	50/60 Hz
功率损耗	at Rated Operating Conditions per Pole 9.5 W
保护极数	1

极数	2P
中性端子位置	Right
拧紧力矩	3.5...4 N·m
利用类别	Connecting and disconnecting under no-load conditions - occasional actuation (AC-20B)
Lock Type	Padlockable
安装类型	DIN-Rail
封口类型	Sealing Wire
Material of Conductor	Copper
提供的选项	No
推荐的螺丝刀	Pozidriv 2
连接容量	Rigid 4...35 mm ² Rigid Stranded 4...50 mm ²
熔断器规格	22x58 mm
	max. 90% with temp. +20 °C 50% with max. temp. +40 °C
额定工作电流AC (I _e)	125 A

Material Compliance

RoHS信息	2CSC444009D2701
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS日期	01/01/2014 0.00.00
REACH Declaration	9AKK108467A9482
REACH Information	True - contains substances > 0.1 mass percentage
REACH Date	20240429
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363

环境条件

周围环境温度	Storage -5...+40 °C Storage Operation -25...+70 °C
防护等级	IP20
耐振动符合IEC 60068-2-6标准	1 mm 2 ... 13 Hz
抗机械冲击符合IEC 60068-2-27标准	15g 18 shocks 11 ms
环境信息	See RoHS Information

尺寸

宽度(模块化垫片数)	4
产品净宽	70 mm
产品净高	112 mm
产品净深	73.26 mm
产品净重	270 g
内深 (t ₂)	73.26 mm

订货信息

1级包装单元	box 2 piece
1级包装 总重	0.54 kg

E-Number (Norway)

1416161

认证及声明（文件编码）

BV认证	9AKK108467A0329
CCC认证	9AKK108467A0344
符合性声明 - CE	2CSC444009D2701
KRS认证	9AKK108467A0338
LR认证	9AKK108467A0332
RINA认证	9AKK107992A0866
UL认证	9AKK107992A1042
认证机构	BV, Korean register, CCC, EAC, UL

Installation

说明书和手册	No document needed
--------	--------------------

Popular Downloads

数据手册，技术资料	2CSC444002B0204
-----------	-----------------

分类

ETIM 8	EC002705 - Holder for cylindrical fuse
ETIM 9	EC002705 - Holder for cylindrical fuse
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85361090
UNSPSC	39121624
e级	V11.0 : 27142121
IDEA 粒度分类代码 (IGCC)	4974 >> Holder for cylindrical fuse
对象分类代码	F

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CSM257183R1801	Fuse link	E 9F22 GG4	1	piece
2CSM259283R1801	Fuse link	E 9F22 GG6	1	piece
2CSM258103R1801	Fuse link	E 9F22 GG8	1	piece
2CSM256923R1801	Fuse link	E 9F22 GG10	1	piece
2CSM259403R1801	Fuse link	E 9F22 GG12	1	piece
2CSM258223R1801	Fuse link	E 9F22 GG16	1	piece
2CSM257043R1801	Fuse link	E 9F22 GG20	1	piece
2CSM259533R1801	Fuse link	E 9F22 GG25	1	piece
2CSM258353R1801	Fuse link	E 9F22 GG32	1	piece
2CSM257173R1801	Fuse link	E 9F22 GG40	1	piece
2CSM259393R1801	Fuse link	E 9F22 GG50	1	piece
2CSM258213R1801	Fuse link	E 9F22 GG63	1	piece
2CSM257033R1801	Fuse link	E 9F22 GG80	1	piece
2CSM259523R1801	Fuse link	E 9F22 GG100	1	piece
2CSM258343R1801	Fuse link	E 9F22 GG125	1	piece

分类

低压产品及系统 → 线路保护产品 → Protection and Safety Devices → Cylindrical Fuse Holders and Fuse Switch Disconnectors



360°