

NLG Tether Shackle, Medium

Product Code:
101602

Max Load:
10 KG / 22 LBS



OVERVIEW

NLG Tether Shackles create a simple and secure tether point on tapered tools such as spanners or wrenches. Available in four sizes and boasting a 10kg load rating, they are a highly versatile tether point that is perfect for a wide range of tool sizes.

VIEW ONLINE

<https://neverletgo.com/products/tether-shackle-medium/>



NLG ID™ Serialised and safe

Simply scan the NLG ID tag with your phone to instantly access certificates, instruction videos and log inspections. (See Specification if included).



Third-party tested and certified

Independent laboratory load testing certificates and Declarations of Conformity are available on request. Please contact team@neverletgo.com.

DESCRIPTION	NLG Tether Shackles create a super durable tether point on any tools that have a narrower mid-section (waist) or pre-manufactured hole. The flush pin ensures that there are no snagging issues - it will take an allen key to get the pin correctly installed. Load rated to 10KG and made from stainless steel these shackles will take an absolute beating every day and come back asking for more. The Tether Shackle is available in four sizes making it a highly versatile tether point, that will work for small spanners right up to large Podgers (spud wrenches).	
FEATURES	Quick and easy installation Constructed from 304 Stainless Steel for excellent corrosion and wear resistance Features a flush pin to prevent snagging and/or accidental release Comes in four sizes	
TECHNICAL SPECIFICATION	Max Load: 10 KG / 22 LBS Safety Standards: ANSI/ISEA 121-2018, CE / UKCA, NS 9611:2022+AC Load Tested and Third-party Certified: Dynamic (2:1 Safety Factor) Unique Serial Number Dimensions: 50mm (L) x 30mm (W) Max Lanyard Length: 200 CM / 78 IN	
RETAIL	EAN (GTIN-13) 5060572180871	UNIT WEIGHT (G) 55
SHIPPING	HS CODE 7326.90.9890	COUNTRY OF ORIGIN Taiwan



Tether Shackle, Medium

Product Code: 101602

View online

<https://neverletgo.com/products/tether-shackle-medium/>

Learn more about:

[Dropped object prevention](#)

[Tool tethering](#)

[Tool lanyards](#)

Useful resources:

[Tool Box](#)

[Tool Tether Guide](#)

[Library](#)

CONTACT

[+44 \(0\)330 016 0030](tel:+44(0)3300160030)

neverletgo.com

INSPECTION

In addition to routine checks before each use, all equipment should undergo regular detailed inspections, conducted and recorded by a competent person using the NLG Inspection Checklist. If any part is worn or shows signs of degradation, immediately retire from service. In the event of a drop, quarantine the equipment for a thorough inspection.

[Click to download Inspection Checklist](#)

LEGAL

NLG makes every effort to ensure the information in this Datasheet is accurate and current. However, NLG reserves the right to change the product specification when necessary. NLG cannot be held responsible for any inaccuracies or omissions.

Copyright © 2023. NLG® and Never Let Go® are registered trademarks.
