

Features

- Heavy duty steel construction
- Fitted with hasp & staple lock
- Fully welded with angled lid
- Lid restraint to prevent lid from falling back
- Non removable sump
- Warning labels
- Conforms to COSHH guidelines
- Dimension 610 x 1170 x 460mm

RS PRO Yellow Lockable Hazardous Substance Floor Chest, 610 x 1170 x 460mm

RS Stock No.: 0440923



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Hazardous Substance Cabinets

Our RS PRO hazardous substance cabinet is designed to provide safe storage for potentially dangerous substances and materials. Featuring steel construction, fully welded integrated sump and angled lid to discourage article placement with a restraint top prevent lid from falling back. Fitted with hasp and staple locking mechanism (padlock not supplied). A non-removable spillage sump is an integral part of the base to contain spillage.

General Specifications

Height	610mm
Width	1170mm
Depth	460mm
Lockable	Yes – hasp and staple fitting
Number of Doors	1 Lid
Number of Shelves	0
Colour	Yellow

Approvals

Declarations	REACH DoC
Standards Met	COSHH

Similar Products

Stock No.	Brand	Product Name	Dimension	No. of Door	Colour
0440936	RS PRO	Hazardous Cupboard 1800x1200x460mm	1800x1200x460mm	2	Yellow
0440911	RS PRO	Hazardous Cupboard 1800x900x460mm	1800x900x460mm	2	Yellow
0440913	RS PRO	Hazardous Cupboard 1200x900x460mm	1200x900x460mm	2	Yellow
0440914	RS PRO	Hazardous Cupboard 900x900x460mm	900x900x460mm	2	Yellow
0440915	RS PRO	Hazardous Cupboard 900x460x460mm	900x460x460mm	1	Yellow
0440917	RS PRO	Hazardous Cupboard 700x900x460mm	700x900x460mm	2	Yellow
0440918	RS PRO	Hazardous Cupboard 700x350x300mm	700x350x300mm	1	Yellow
0440920	RS PRO	Mobile Hazardous Cupboard 1040x900x460mm	1040x900x460mm	2	Yellow
0440921	RS PRO	Mobile Hazardous Cupboard 840x900x460mm	840x900x460mm	2	Yellow
0440923	RS PRO	Flo.Chest Hazar. Cupboard 610x1170x460mm	610x1170x460mm	N/A	Yellow
0440924	RS PRO	Wall Moun. Hazar. Cupboard 570x850x255mm	570x850x255mm	2	Yellow
0440926	RS PRO	Galvanised Extra Shelves 1200x460mm	1200x460mm	N/A	Yellow
0440927	RS PRO	Galvanised Extra Shelves 900x460mm	900x460mm	N/A	Yellow
0440929	RS PRO	Galvanised Extra Shelves 460x460mm	460x460mm	N/A	Yellow
0440930	RS PRO	Galvanised Extra Shelves 350x300mm	350x300mm	N/A	Yellow
0440932	RS PRO	Stand to suit 900x460mm	900x460mm	N/A	Yellow
0440933	RS PRO	Stand to suit 460x460mm	460x460mm	N/A	Yellow
0440935	RS PRO	Stand to suit 350x300mm	350x300mm	N/A	Yellow