


11911 DSR-25-180-P Semi-rotary drive - Series: All



11911 DSR-25-180-P Semi-rotary drive - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	383849	DSR/L-25-180-P Set of wearing parts	Spare parts: 17, 18, 20, 22, 29, 30	1	PC
1	239636	DSR-25- Cover cap		1	PC
2	200671	ISO 4762-M5X16-10.9 Socket head screw	Tightening torque 1 Nm / 0.7 lbf ft	2	PC
3	200584	DIN 127-B-5 Split washer		2	PC
4	237956	DSR- 25- Trip cam		2	PC
5	238646	DSR- 25- 180P:BEDRUCKT Cover cap		1	PC
6	229181	DIN 6799-9 Retaining washer		1	PC
7	338759	DSR- 25- 180P Disc		1	PC
8	232523	DSR-25-180-P Stop		2	PC
9	226488	XF+D625-61802-2RS Deep groove ball bearing		2	PC
10		DSR-25:MA Housing	Not available	1	PC
11	332262	DSR- 25- 180P Shaft		1	PC
12	229183	A-4X4X25-1.0503+C Feather key DIN6885		1	PC
13		FWSR- 25 Push-on flange	Not available separately, see position 16	1	PC
14	200583	DIN 127-B-4 Split washer		1	PC
15	223162	ISO 4762-M4X14-8.8 Socket head screw		1	PC
16	13240	FWSR-25 Push-on flange		1	PC
17		DSR-25 Inner shell	Not available separately, see position A Grease using during assembly. See position 29	1	PC
18		DSR-25-180-P Vane module	Not available separately, see position A Grease using during assembly. See position 29	1	PC
19	679189	DSR-25 Intermediate piece	Grease using during assembly. See position 29	1	PC
20		DSR- 25- 180P Seal	Not available separately, see position A Grease using during assembly. See position 29	1	PC
21		ISO 4762-M6X25-A2-70 Socket head screw	Not available	1	PC
22		DSR- 25- 180P Cushioning plate	Not available separately, see position A Grease using during assembly. See position 29	1	PC
23		DSR-25:CO2 Sub-base	Not available	1	PC
24	200687	ISO 4762-M6X18-10.9 Socket head screw	Tightening torque 10 Nm / 7.4 lbf ft Use locking compound. See position 30	2	PC
25		HSR- 25-FW Foot	Not available separately, see position 26	1	PC
26	30925	HSR-25-FW Foot mounting		1	PC

Pos.	Part no.	Type	Note	Qty.	Unit
27		FSR- 25 Flange	Not available separately, see position 28	1	PC
28	13237	FSR-25 Flange mounting		1	PC
29	665354	LUB-KB1-SILIKONFREI-20ML Lubricating grease		1	PC
30	8181256	CYBERBOND TM44 TB1ML Adhesive bonding agent		1	PC