

AF73 - Araflame Work Lightweight FR

Coverall

Collection: Araflame™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Araflame Work: 93% Meta Aramid, 5% Para Aramid, 2% Carbon Fibre, 150g

Outer Carton: 18



Product information

This super lightweight coverall offers outstanding flame resistant protection. The Araflame fabric is soft and breathable but provides excellent tear and tensile strength. Ideal for a variety of industries including oil and gas, petrochemical and many more. The coverall's features include triple stitching throughout, secure pockets and waist elastication for ease of movement.

Araflame™ Work

Araflame™ Work has been developed for comfort and performance. Certified to several international standards, these garments offer outstanding protection at all times. The high quality fabric combined with the ergonomic fit provide all day comfort and style.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, F1)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 3.8 CAL/CM², ATPV 4.5 CAL/CM²)

EN 17353 Type B2

ASTM F1959/F1959M-12 (ATPV 5.9 CAL/CM² (HAF 63.1%))

Features

- Inherent flame resistant qualities will not diminish with washing
- Protection against radiant, convective and contact heat
- Two back patch pockets
- Triple-stitched seams for extra durability
- Durable, strong and long lasting brass zips
- Hook and loop cuffs for a secure fit
- Sew on flame resistant industrial wash tape
- Radio loops for easy clipping of a radio
- Sleeve pocket
- Two-way front durable brass zip for easy access
- 8 pockets for ample storage

AF73 - Araflame Work Lightweight FR Coverall
Commodity Code: 6211331000

Test House

Aitex (Notified Body No.: NB: 0161)
 Plaza Emilio Sala 1
 , ESPAGNE
 Cert No: 19/1623/01/0161

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
AF73RER32	Red	43.0	28.0	50.0	0.7300	0.0602	5036108331277	25036108819632
AF73RER34	Red	43.0	28.0	50.0	0.7890	0.0602	5036108327898	25036108816693
AF73RER36	Red	43.0	28.0	50.0	0.7700	0.0602	5036108280087	25036108770124
AF73RER38	Red	43.0	28.0	50.0	0.7620	0.0602	5036108280094	25036108770131
AF73RER40	Red	43.0	28.0	50.0	0.7660	0.0602	5036108280100	25036108770148
AF73RER42	Red	43.0	28.0	50.0	0.7870	0.0602	5036108280117	25036108770155
AF73RER44	Red	43.0	28.0	50.0	0.8260	0.0602	5036108280124	25036108770162
AF73RER46	Red	43.0	28.0	50.0	0.8080	0.0602	5036108280131	25036108770179
AF73RER48	Red	43.0	28.0	50.0	0.8560	0.0602	5036108280148	25036108770186
AF73RER50	Red	43.0	28.0	50.0	0.8500	0.0602	5036108280155	25036108770193
AF73RER52	Red	43.0	28.0	50.0	0.8740	0.0602	5036108280162	25036108770209
AF73RER54	Red	43.0	28.0	50.0	0.8940	0.0602	5036108280179	25036108770216