



Pullers

11250

Product no. **71025001**
GTIN **4018754341948**
Model **11250/1**

Label.

Puller Clamping w.280mm x Clamping d.390mm

Properties.

- two-armed
- with swivelling extractor hooks
- extractor hooks and beam are connected by movable tabs
- for V-belt pulleys and flywheels on long shafts
- when the spindle is tightened, the extractor hooks are tensioned and tighten
- variable clamping depth possible by adjusting the extractor hooks
- nitrided spindle, no lubrication required, maintenance-free
- zinc plated

Benefits.

The greater the extraction force, the stronger the grip of the extractor hooks on the workpiece to be extracted.

Particularly suitable for removing V-belt pulleys and flywheels mounted on longer shafts.

Easy on the workpiece thanks to even force distribution.

Adjustable clamping depth for universal use.

The nitrided surface of the spindle allows it to move easily so it does not require additional lubrication.


Product highlights.

For increased safety.

Thoughtfully designed, die-forged and precisely machined, hardened and tempered on state-of-the-art machines - the STAHLWILLE puller range offers numerous products for a wide range of applications. For example, terminal pullers, pullers for ball joints, counter stays or ball joint extractors - always in premium quality.



Technical drawing.



Technical attributes.

External hex drive (mm)	22 mm
Size	1
Number of hooks	2
max. load	8 t
Clamping depth (h) mm	390 mm
Spindle thread size	G 1/2 x 250
Span mm (w)	280 mm

Logistics data.

Depth mm (IFS)	455
Width mm (IFS)	230
Height mm (IFS)	53
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	590
Width (packaged, mm)	395
Height (packaging, mm)	110
Volume (packaged, dm ³)	25.6355 dm ³
Product no.	71025001
Weight (gross, kg)	6,100
Weight PAP (kg)	1,138
Weight PVC (kg)	0,000
GTIN	4018754341948
Country of origin AWR	GERMANY

Region of origin	Nordrhein-Westfalen
Customs tariff no.	82055980
Packing standard	1
Weight (g)	4983 g

Variants.

Product no.	Model No. (ERP)	Description	GTIN
71025001	11250/1	Puller Clamping w.280mm x Clamping d.390mm	4018754341948
71025002	11250/2	Puller Clamping w.420mm x Clamping d.480mm	4018754341955

GTIN.



Spare part(s), spare part(s) for.



79281004
Puller spindle

Images.





STAHLWILLE Eduard Wille GmbH

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal