
# Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



LVS08293

EAN Code: 3606481878410

# Main

Range	PrismaSeT	
Range of product	PrismaSeT G	
Product or component type	Door	
Range compatibility	PrismaSeT PrismaSeT G duct	
Provided equipment	door handle keylock (key 405) other keylock and insert to be ordered separately 3 hinge	
type of door	Transparent	
IP degree of protection	IP43 with door, canopy and IP43 gasket IP30 without door IP40 with door IP41 with door and canopy	

# Complementary

installation description	Floor-standing duct - width 300 mm	
Door opening side	Reversible	
Number of locks	3	
door opening angle	130 °	
Number of vertical modules [50 mm]	30	
Enclosure material	Handle: polyamide Glass Cover frame: treated sheet steel	
Quantity per set	Set of 1	
Height	1680 mm	
Width	300 mm	
Depth	36 mm	
Net weight	6.48 kg	
Material	Glass	
Surface finish	Matt Textured	
Colour	White (RAL 9003)	

## **Environment**

IK degree of protection IK08 conforming to EN/IEC 62262

	IEC 61439-2	
Standards	IEC 61439-1	

# **Packing Units**

_	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	34.000 cm
Package 1 Length	159.000 cm
Package 1 Weight	7.749 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	30
Package 2 Height	85.000 cm
Package 2 Width	120.000 cm
Package 2 Length	202.000 cm
Package 2 Weight	260.500 kg

# **Logistical informations**

Country of origin FF

# **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

### Environmental Data explained >

How we assess product sustainability >

# 

Environmental Disclosure

Product Environmental Profile

### **Use Better**


Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	53da272d-b040-4851-8009-84e538bee882
REACh Regulation	REACh Declaration

### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

# **Technical Illustration**

### **Dimensions**



- All dimensions are approximate and are ir
   Also see technical documentation.