

Universe	Professional
Type	Verticality
Category	Harnesses
Subcategory	Fall arrest and work positioning harness



VOLT® International Version

The VOLT fall-arrest and work positioning harness is very quick to put on, thanks to the FAST LT PLUS buckles that allow it to be donned with both feet on the ground. The wide, semi-rigid waistbelt and leg loops provide excellent support. Its lightweight, breathable construction maximizes air flow. It features a textile dorsal attachment point designed for connecting a self-retracting fall-arrest system. It is certified to U.S. and European standards.



The waistbelt and leg loops are equipped with FAST LT PLUS buckles, allowing the harness to be easily donned while keeping both feet on the ground. These buckles retain their adjustment settings between donnings.



The textile dorsal attachment point allows connection of a self-retracting fall-arrest system.



The wide, semi-rigid waistbelt and leg loops provide excellent support. Its lightweight, breathable construction maximizes air flow.



The waistbelt and leg loops are equipped with FAST LT PLUS buckles for quick and easy fastening and unfastening without loss of adjustment, even while wearing gloves. The buckle's locking system limits the risk of accidental unfastening.

Short Description Fall-arrest and work positioning harness

Selling Points

- Quick and easy donning:
 - Waistbelt and leg loops equipped with FAST LT PLUS buckles for quick and easy fastening and unfastening without loss of adjustment, even while wearing gloves; these buckles allow the harness to be donned very easily, with both feet on the ground
 - DOUBLEBACK self-locking buckles on waistbelt and shoulder straps for precise adjustment
 - Leg loop foam position can be adjusted for ideal positioning
- Comfortable throughout the workday:
 - Wide, semi-rigid waistbelt and leg loops for excellent support and lightweight, breathable construction to maximize air flow
 - Padded shoulder straps are widely spaced to reduce neck chafing and help distribute the load over the shoulders when the waistbelt is loaded
 - Textile dorsal attachment point for connecting a self-retracting fall-arrest system
 - Side slots allow a seat to be installed for greater comfort during prolonged suspension
- Easy to use:
 - Side attachment points can be folded down to prevent accidental snagging when not in use
 - Stowing system for the MGO connectors on fall-arrest lanyards are located on each shoulder strap; in the event of a fall, the system releases the MGO connectors and allows the absorber to be deployed
 - Equipment loops, as well as slots for CARITool tool holder and TOOLBAG tool pouch make it easy to organize work tools

Specification

- Side attachment points: For attaching a positioning lanyard for use in double mode
 - Sternal attachment point: For attaching a fall-arrest system
 - Metal dorsal attachment point: For attaching a fall-arrest system
 - Textile dorsal attachment point: For attaching a self-retracting fall-arrest system
 - Rear waistbelt attachment point: For attaching a restraint lanyard
 - Certification(s): ANSI Z359.11, CSA Z259.10, CE EN 361, CE EN 358, UKCA
 - Material(s): Nylon, polyester, aluminum, steel
-

Specifications by reference

Reference(s)	C072CA00	C072CA01	C072CA02
Color(s)	Black/Yellow	Black/Yellow	Black/Yellow
Size	0	1	2
Waist belt	65-80 cm	70-93 cm	83-120 cm
Leg loops	44-59 cm	47-62 cm	50-65 cm
Stature	160-180 cm	165-185 cm	175-200 cm
Weight	2300 g	2350 g	2430 g
Made in	RO	RO	RO
Guarantee	3 years	3 years	3 years
Inner Pack Count	1	1	1
Quantity Per Box	3	3	3
EAN	3342540831018	3342540831025	3342540831032

Spare part(s) Lanyard connector holder

Accessory(ies) Seat for VOLT® harnesses