

DELTA FLAT IP44, SM DARK GRAY/LIGHT GRAY  
SCHUKO OUTLET 3FOLD HORIZONTAL, 10/16A 250V  
W. SCREWLESS TERMINALS W. HINGED LID,  
75X201MM



Model		
Design of the product		SCHUKO
Cover version		complete enclosure
Design of the special power supply unit		without special current supply
Design of the socket / according to VDE 0620 for severe conditions		No
Design of the phase tap		Without
General technical data		
Marking / of socket outlet		without imprint
Mounting type		fixing with screw
Surface processing		others
Material		others
Protection class		
Protection class IP		IP44
Main circuit		
Operating frequency		
• minimum	Hz	50
• maximum	Hz	50
Operating voltage / Rated value	V	250
Operating current / Rated value	A	16
Appearance		
Color		grey
Product details		

<b>Product component</b>		
• Ejection equipment		No
• Labeling field		No
• Increased touch protection		No
• Fault current protection		No
• miniature fuse		No
• Integrated / functional lighting		No
• Integrated / Light source		No
• Integrated / orientation lighting		No
• Hinged lid		Yes
<b>Product property</b>		
• lockable		No
• halogen-free		Yes
• transparent		No

<b>Product function</b>		
<b>Product function</b>		
• Socket selectable		No
• Overvoltage protection		No

<b>Number</b>		
<b>Number of units</b>		3
<b>Number of sockets / switchable</b>		0

<b>Connections</b>		
<b>Arrangement of contacts / diagonal</b>		No
<b>Type of electrical connection</b>		plug terminal

<b>Mechanical Design</b>		
<b>Height</b>	mm	75
<b>Width</b>	mm	198
<b>Depth</b>	mm	54
<b>Mounting type</b>		surface mounted
<b>Material / of the enclosure</b>		plastic

<b>General Product Approval</b>			<b>Test Certificates</b>		
				<a href="#">Type Test Certificates/Test Report</a>	<a href="#">other</a>
ÖVE	GOST	VDE			

<b>Further information</b>		
<b>Information- and Downloadcenter (Catalogs, Brochures,...)</b>		
<a href="http://www.siemens.com/lowvoltage/catalogs">http://www.siemens.com/lowvoltage/catalogs</a>		
<b>Industry Mall (Online ordering system)</b>		
<a href="https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5UB4731">https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5UB4731</a>		

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/5UB4731/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5UB4731](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5UB4731)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

05.05.2015