




PRODUCT-DETAILS

# IS2-ES2225MF4K

## Control and Automation Board



| 概要信息        |                                                                                   |
|-------------|-----------------------------------------------------------------------------------|
| 产品型号        | IS2-ES2225MF4K                                                                    |
| 产品ID        | ES2225MF4K                                                                        |
| 欧洲商品编号(EAN) | 8015646743770                                                                     |
| 目录说明        | Control and Automation Board                                                      |
| 详细描述        | Cabinets for compartments 2200x500x1200mm (HxDxW) with Cable container<br>W=400mm |

| 技术参数   |                                                             |
|--------|-------------------------------------------------------------|
| 标准     | IEC 62208, IEC 61439-1-2<br>NEMA 1, 3R, 12                  |
| 配置类型   | 6. Cabinet for configuration with compartments              |
| 外壳类型   | Pre assembled - cabinet for configuration with compartments |
| 安装类型   | Pre assembled                                               |
| 产品应用类型 | 5B5B10B180                                                  |
| 柜门类型   | Double                                                      |
| 表面处理   | Orange Peel, RAL 7035                                       |
| 柜门表面处理 | Opaque                                                      |

|            |                       |
|------------|-----------------------|
| 材料         | Sheet Steel Metal     |
| 评论         | ETIM                  |
| RAL Number | RAL 7035 - Light Grey |

Material Compliance

|        |            |
|--------|------------|
| RoHS信息 | 1STC860065 |
| RoHS日期 | 20140108   |

环境条件

|      |                        |
|------|------------------------|
| 防护等级 | acc. to IEC 60529 IP55 |
| 环境信息 | 1STC804013D0209        |

尺寸

|                        |             |
|------------------------|-------------|
| 产品净宽                   | 1210 mm     |
| 产品净高                   | 2311.5 mm   |
| 产品净深                   | 1240 mm     |
| 产品净重                   | 130.5190 kg |
| Reference Depth/Length | 500 mm      |
| Reference Height       | 2200 mm     |
| Reference Width        | 1200 mm     |

订货信息

|         |            |
|---------|------------|
| 1级包装单元  | 1 piece    |
| 1级包装 总重 | 138.850 kg |

认证及声明（文件编码）

|            |            |
|------------|------------|
| 符合性声明 - CE | 1STC860113 |
|------------|------------|

Installation

|        |                 |
|--------|-----------------|
| 说明书和手册 | 1STM604121R0006 |
|--------|-----------------|

Popular Downloads

|            |                 |
|------------|-----------------|
| 数据手册, 技术资料 | 1STC804013D0209 |
|------------|-----------------|

分类

|                |                                                             |
|----------------|-------------------------------------------------------------|
| ETIM 8         | EC000261 - Enclosure/cabinet (empty)                        |
| ETIM 9         | EC000261 - Enclosure/cabinet (empty)                        |
| WEEE 类别        | 4. Large Equipment (Any External Dimension More Than 50 cm) |
| WEEE B2C / B2B | Business To Business                                        |
| CN8            | 85381000                                                    |

|        |                  |
|--------|------------------|
| e级     | V11.1 : 27180101 |
| 对象分类代码 | U                |

分类

低压产品及系统 → 箱壳类产品 → 控制和自控板 → Enclosures - Baying (Horizontal Joining) → IS2

