

INDEX

ATTACHMENT PLUG:

NEMA CONFIGURATION

Cat. No.	Config.	Cord AWG	Electrical A/V.	Sec	Fig.	C-UL
WS-001	5-15	18,17,16,14,12/3	10,12,13,15,15/125	1	1	Yes
WS-001F	5-15	18,17,16,14,12/3	10,12,13,15,15/125	1	1	Yes
WS-001G	5-15	18,17,16,14,12/3	10,12,13,15,15/125	1	1	Yes
WS-001I	6-15	18,16,14,12/3	10,13,15/250	1	4	Yes
WS-001I	5-20	18,16,14,12/3	10,13,20,18/125	1	-	Yes
WS-001I	6-20	18,16,14,12/3	10,13,18,20/250	1	-	Yes
WS-001C	6-20P	18,16,14,12/3	10,13,18,20/250	1	5	Yes
WS-001C	5-20P	18,16,14,12/3	10,13,18,20/125	1	-	Yes
WS-001C	6-15P	18,16,14,12/3	10,13,15,15/250	1	-	Yes
WS-001C	5-15P	18,16,14,12/3	10,13,15,15/125	1	-	Yes
WS001D(Series)	6-20P	18,16,14,12/3	10,13,18,20/250	1	-	Yes
WS001D(Series)	5-20P	18,16,14,12/3	10,13,18,20/125	1	-	Yes
WS001D(Series)	6-15P	18,16,14,12/3	10,13,15,15/250	1	-	Yes
WS001D(Series)	5-15P	18,16,14,12/3	10,13,15,15/125	1	-	Yes
WS-001H	5-15	18,16,14,12/3	10,13,15/125	1	2	Yes
WS-001H	6-15	18,16,14,12/3	10,13,15/250	1	2	Yes
WS-001H	5-20	18,16,14,12/3	10,13,20/125	1	2	Yes
WS-001H	6-20	18,16,14,12/3	10,13,20/250	1	2	Yes
WS-001H-6	5-15	18,16,14/3	10,13,15/125	1	-	Yes
WS-001H-7	5-15	18,16,14/3	10,13,15	1	26	Yes
WS-001H-8	5-15	18,16,14/3	10,13,15	1	28	Yes
WS-001H-10	5-15	18,16,14/3	-	1	29	Yes
WS-001M	5-15P	18,14,12/3	10,15,15/125	1	6	Yes
WS-001M	5-20P	18,14,12/3	10,18,20/125	1	6	Yes
WS-001M	6-15P	18,14,12/3	10,15,15/250	1	6	Yes
WS-001M	6-20P	18,14,12/3	10,18,20/250	1	6	Yes
WS-004	1-15	18,16/2	10,13/125	1	7	Yes
WS-004A	1-15	18,17,16,14/2	10,12,13,15/125	1	3	Yes
WS-004C	1-15	18,17,16,14/2	10,12,13,15/125	1	3	Yes
WS-004C-3	1-15	18,17,16,14/2	10,12,13,15/125	1	3	Yes
WS-004-L	1-15	18,17,16,14/2	10,12,13,15/125	1	22	Yes
WS-004-R	1-15	18	10/125	1	33	Yes
WS-004-S	1-15	18/2	7/125	1	34	Yes
WS-004-Q	1-15	18,16,14/2	10,13,15/125	1	35	Yes
WS-117	L5-20P	14,12,10/3	18,20,20/125	1	8	Yes
WS-117-2	L5-20P	12, 10	20, 20/125	1	-	Yes
WS-118	L5-15P	16,14,12,10/3	18,15,15,15/125	1	9	Yes
WS-119	L6-20P	16,14,12,10,8/3	13,18,20,20,20/250	1	9	Yes
WS-119-2	L6-20P	12, 10	20, 20/250	1	-	Yes
WS-120	L6-30P	16,14,12,10,8/3	13,18,25,30,30/250	1	9	Yes
WS-120-2	L6-30P	12, 10	25, 30/250	1	-	Yes
WS-121	L5-30P	16,14,12,10,8/3	13,18,25,30,30/125	1	9	Yes
WS-121-2	L5-30P	12, 10	25, 30/125	1	-	Yes
WS-122	L14-30P	16,14,12,10,8/4	10,15,20,25,30/250	1	9	Yes
WS-122-2	L14-30P	12, 10	25, 30/250	1	-	Yes
WS-123	L6-15P	16,14,12,10,8/3	13,15,15,15,15/250	1	9	Yes
WS-129	L14-20P	16,14,12,10,8/4	10,15,20,20,20/250	1	9	Yes
WS-129-2	L14-20P	12, 10	20, 20/250	1	-	Yes
WS-130	L1520PPH	16,14,12,10,8/4	10,15,20,20,20/250	1	9	Yes
WS-130-2	L15-20P	12, 10	20,20/250,3-	1	-	Yes
WS-131	L15-30P	16,14,12,10,8/4	10,15,20,30,30/250	1	9	Yes
WS-131-2	L1530PPH	12, 10	25,30/250,3-	1	-	Yes
WS-225	L21-30P	10	30A, 120/208 V, 3 PH	1	30	Yes
WS-226	L7-15P	18,16,14,12,10/3	10,13,15,15,15/277	1	25	Yes
WS-234	L21-20	12,10/5	20.20/208,250	1	-	Yes
WS-004E	1-15(EMI)		18/27/125	1	10	Yes