

FR21 - Bizflame Work Lightweight FR

Coverall

Collection: Bizflame™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizflame Work: 99% Cotton, 1% Carbon Fibre, 210g

Outer Carton: 14



Product information

This coverall is perfect for the extra warm weather demands of the offshore industry. Constructed with a lighter weight highly innovative flame-resistant twill fabric.

Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2,F1)

EN ISO 11611 Class 1 (A1+A2)

EN 1149 -5

EN 17353 Type B2

ASTM F1959/F1959M-12 (ATPV = 9.1cal/cm²)

Features

- Lightweight for enhanced wearer comfort
- Protection against radiant, convective and contact heat
- Rule pocket
- Two back patch pockets
- Durable, strong and long lasting brass zip
- Action back for extra freedom of movement
- Hook and loop cuffs for a secure fit
- Sleeve pocket
- 10 pockets for ample storage
- Two tier knee pad pockets allowing two positioning options
- Two-way zip for quick and easy access

FR21 - Bizflame Work Lightweight FR Coverall
Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/12375-06/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR21RERXS	Red	43.0	28.0	58.0	1.0330	0.0698	5036108298822	25036108788440
FR21RERS	Red	43.0	28.0	58.0	1.0780	0.0698	5036108213191	25036108699036
FR21RERM	Red	43.0	28.0	58.0	1.1080	0.0698	5036108213184	25036108699029
FR21RERL	Red	43.0	28.0	58.0	1.1890	0.0698	5036108213177	25036108699012
FR21RERXL	Red	43.0	28.0	58.0	1.2400	0.0698	5036108213207	25036108699043
FR21RERXXL	Red	43.0	28.0	58.0	1.2430	0.0698	5036108213252	25036108699050
FR21RERXXXL	Red	43.0	28.0	58.0	1.2810	0.0698	5036108213269	25036108699067
FR21RER4XL	Red	43.0	28.0	58.0	1.3800	0.0698	5036108299188	25036108788709