

Charge 'n' Go Magnetic Wireless Power Bank 5000mAh



Part Number: 32240, 32241, 32242, 32243, 32244

Description

The Verbatim Charge 'n' Go 5000mAh Power Bank features a super-slim 9.6mm body, delivering optimal portability without sacrificing performance.

Its advanced features include 15W magnetic wireless charging, PD20W capabilities, and a versatile bi-directional Type-C port, ensuring swift and efficient charging. The LED indicator provides users with easy-to-monitor power status and the additional metal ring can be attached to the phone or phone case to provide a strong magnetic hold if required.

Designed for versatility, Verbatim Power Banks are perfect companions for travel, commuting, events, and outdoor activities, offering a dependable on-the-go energy solution.

- Super-slim body thickness - only 9.6mm
- High Density Battery
- Battery Nominal capacity: 5000 mAh
- 15W Magnetic Wireless
- PD 20W capabilities
- LED Indicator, Easy to Read Power Volume
- Bi-direction Fast Charging & Discharging Type-C Port



Charge 'n' Go Magnetic Wireless Power Bank 5000mAh



Part Number: 32240, 32241, 32242, 32243, 32244

Specifications:

Battery Capacity: 5000mAh

Rated Capacity: Based on 5V-2.4A output - Around 3000mAh

USB-C PD 3.0 Input:

5 V – 2.4 A, 9 V – 2.0 A (18 W max)

USB-C PD 3.0 Output:

5 V – 2.4 A, 9 V – 2.22 A, 12 V – 1.67 A, (20 W max)

Wireless Output: 5W, 7.5W, 10W, 15W

Total PD Output: 20 W max.

Supports PD 3.0, QC 3.0, Apple2.4A, BC1.2, DCP, AFC

Storage Temperature: Under normal temperature conditions: -10 ~45°C;
charging and discharging every 3-4months



Languages

Front of pack: English (Product description also in French)

Back of pack: English, English; French; German; Dutch; Italian; Spanish;
Portuguese; Polish; Russian; Czech; Hungarian; Slovakian; Croatian; Serbian;
Romanian; Turkish; Traditional Chinese; Simplified Chinese; Korean;
Japanese

Quick Installation Languages:

EN/FR/DE + Multilingual support text

Pack Contents:

- Power Pack
- Metallic Ring
- USB-C to USB-C 30cm cable

Charge 'n' Go Magnetic Wireless Power Bank 5000mAh



Reorder No.	Description	Barcode	EAN-128	EAN-14
32240	Verbatim Charge 'n' Go Magnetic Wireless Power Bank 5000 Black	023942322405	(02)00023942322405(37)10(91)843 (02)00023942322405(37)20(91)843	20023942322409 50023942322400
32241	Verbatim Charge 'n' Go Magnetic Wireless Power Bank 5000 Green	023942322412	(02)00023942322412(37)10(91)843 (02)00023942322412(37)20(91)843	20023942322416 50023942322417
32242	Verbatim Charge 'n' Go Magnetic Wireless Power Bank 5000 Blue	023942322429	(02)00023942322429(37)10(91)843 (02)00023942322429(37)20(91)843	20023942322423 50023942322424
32243	Verbatim Charge 'n' Go Magnetic Wireless Power Bank 5000 Pink	023942322436	(02)00023942322436(37)10(91)843 (02)00023942322436(37)20(91)843	20023942322430 50023942322431
32244	Verbatim Charge 'n' Go Magnetic Wireless Power Bank 5000 Grey	023942322443	(02)00023942322443(37)10(91)843 (02)00023942322443(37)20(91)843	20023942322447 50023942322448



Charge 'n' Go Magnetic Wireless Power Bank 5000mAh**Ordering information:**

Product Dimensions L x W x H	65.2 x 9.6 x 104 mm
Product Weight	124 grams
Units per Pack	1
Pack Dimensions L x W x H	90 x 25 x 153 mm
Pack Weight	172 grams
Units per Inner Carton	10
Inner Carton Dimensions L x W x H	275x150x117 mm
Inner Cartons Weight	1850 grams
Units per Outer Carton	20
Outer Carton Dimensions L x W x H	295 x 170 x 264 mm
Outer Cartons Weight	4000 grams
Outer Cartons per Layer	12
Layers per Pallet	6
Units per Pallet	1440

