



Wire draw mechanism for wire draw encoders

SICK
Sensor Intelligence.



Ordering information

Other models and accessories → www.sick.com/Wire_draw_mechanism_for_wire_draw_encoders

- **Product segment:** Wire draw mechanism
- **Product family:** wire draw mechanism for wire draw encoders

Description	Items supplied	Type	Part no.
EcoLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 1.25 m	Without encoder, 2 x fixing clamp (0061W01-00:21), 2 x fixing screw (DIN912-M3x6), 1 x Woodruff key DIN 6888 2x2.6	MRA-G055-101D4	5324019
EcoLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 1.65 m	Without encoder	MRA-G055-101D4S03	5341052
EcoLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 10 m	Without encoder	MRA-G190-110D3	5326242
EcoLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 3 m	Without encoder	MRA-G080-103D3	5322778
EcoLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 5 m	Without encoder	MRA-G130-105D3	5322779
HighLine wire draw mechanism for face mount flange with 10 mm shaft, measuring range 0 m ... 10 m	Without encoder	MRA-F130-410D2	6029790
HighLine wire draw mechanism for face mount flange with 10 mm shaft, measuring range 0 m ... 10 m, reinforced spring assembly	Without encoder	MRA-F130-410D2S01	6078479
HighLine wire draw mechanism for face mount flange with 10 mm shaft, measuring range 0 m ... 20 m	Without encoder	MRA-F130-420D1	6029791
HighLine wire draw mechanism for face mount flange with 10 mm shaft, measuring range 0 m ... 2 m	Without encoder	MRA-F080-402D2	6029788
HighLine wire draw mechanism for face mount flange with 10 mm shaft, measuring range 0 m ... 30 m	Without encoder	MRA-F130-430D1	6029792
HighLine wire draw mechanism for face mount flange with 10 mm shaft, measuring range 0 m ... 50 m	Without encoder	MRA-F190-450D2	6029793
HighLine wire draw mechanism for face mount flange with 10 mm shaft, measuring range 0 m ... 5 m	Without encoder	MRA-F130-405D2	6029789
		MRA-F130-405D2S01	6065411
HighLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 10 m	Without encoder	MRA-F130-110D2	6028627
HighLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 15 m	Without encoder	MRA-F130-115D2	6072738
HighLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 20 m	Without encoder	MRA-F130-120D1	6028628
HighLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 2 m	Without encoder	MRA-F080-102D2	6028625

Description	Items supplied	Type	Part no.
HighLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 30 m	Without encoder	MRA-F130-130D1	6028629
HighLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 3 m	Without encoder	MRA-F080-103D2	6030125
HighLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 50 m	Without encoder	MRA-F190-150D2	6028630
HighLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 5 m	Without encoder	MRA-F130-105D2	6028626
HighLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 60 m	Without encoder	MRA-F190-160D2	6073783
VarioLine wire draw mechanism for servo flange with 6 mm shaft, measuring range 0 m ... 3 m	–	MRA-V080-103D3	5347779

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com