

IB132-Y



IB132-Y Enclosure

General Information

Extended Product Type	IB132-Y
Product ID	1SAM201911R1011
EAN	4013614421624
Catalog Description	IB132-Y Enclosure
Long Description	IB132-Y enclosure is suitable for manual motor starter MS116/MS132. The combination of manual motor starter and enclosure allows to setup all required control and protection functions for single machine installations. The enclosure has a IP65 degree of protection. Additional mounting of auxiliary and signalling contacts, shunt trips and undervoltage release is possible. The handle is up to 3-times lockable in OFF position.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	39269097

Popular Downloads

Data Sheet, Technical Information	1SBC100173C0201
Instructions and Manuals	2CDC131028M6804
Dimension Diagram	1SAM200441F0001

Dimensions

Product Net Width	120 mm
Product Net Height	120 mm
Product Net Depth / Length	195 mm
Product Net Weight	0.37 kg

Technical

Contact Position Indication	ON / OFF / TRIP
Actuator Type	Rotary Handle
Color	Yellow / Red
Degree of Protection	IP65
Standards	CSA 22.2 No. 14 IEC/EN 60947-1 IEC/EN 60947-4-1 UL 508

Product Name	Enclosure
Suitable For	MS116 MS132
Suitable for Product Class	Manual Motor Starter
Accessory Group	Mechanical
Accessory Type	Enclosure
Remarks	For detailed specification see installation instruction

Technical UL/CSA

Enclosure Type UL/CSA	12
-----------------------	----

Environmental

Ambient Air Temperature	Operation 0 ... +40 °C Storage -50 ... +80 °C
RoHS Status	Following EU Directive 2011/65/EU

Certificates and Declarations (Document Number)

cUL Certificate	cUL_E137861
Declaration of Conformity - CE	1SAD938503-0196 1SAD938504-0197 1SAD938506-0188 1SAD938507-0183 1SAD938513-0125 1SAD938520-0060
GOST Certificate	1SAA937000-2703
Instructions and Manuals	2CDC131028M6804
RoHS Information	1SAD938517-0060
UL Certificate	UL_E137861

Container Information

Package Level 1 Width	129 mm
Package Level 1 Depth / Length	129 mm
Package Level 1 Height	141 mm
Package Level 1 Gross Weight	0.435 kg
Package Level 1 EAN	4013614421624
Package Level 1 Units	box 1 piece

Classifications

ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC000712 - Empty enclosure for switchgear
ETIM 6	EC000712 - Empty enclosure for switchgear
ETIM 7	EC000712 - Empty enclosure for switchgear
eClass	7.0 27371301
UNSPSC	39121334
IDEA Granular Category Code (IGCC)	4492 >> Modular electrical enclosure
E-Number (Sweden)	3112074

Categories

Low Voltage Products and Systems → Control Products → Manual Motor Starters → Manual Motor Starters Accessories

