



Handling protection

TITAN 850



GRIP & PROOF
TECHNOLOGY

EN388



4132XP

CATEGORY 2



DEXTERITY

EN420:
5/5

Shock protection : specific areas are reinforced to bring cushioning protection and comfort where you need it (Upper Thumb, Knuckle, Base fingers & Palm)

SPECIFIC ADVANTAGES

Impact protection

- Shock protection : specific areas are reinforced to bring cushioning protection and comfort where you need it (Upper thumb, Knuckles, Base fingers & Palm)



Durability

- Durability in use : Long lasting coating, gloves stay clean due to their liquid resistance, suppleness guaranteed even after drying



Productivity

- Grip overtime thanks to our specific technology
- Grip and Proof coating ensures an excellent grip in very oily environment . It also reduces muscle strain and boosts productivity



Skin protection

- Grease & Oilproof for better skin protection thanks to our specific technology
- Free of harmful substances: DMF Free

INDUSTRIES

- Transport, logistics
- Manufacturing
- Industrial equipment / Metal transformation
- Mining / Utilities / Transportation
- Industrial maintenance
- Installation of industrial equipments

APPLICATIONS


- Assembling of heavy parts
- Maintenance
- Handling oily mechanical parts
- Machining of heavy parts
- Mechanical maintenance
- Handling of thick metal sheets
- Machine tool manufacturing
- Metal working
- Handling heavy metal sheets
- Goods handling on loading bays, docks, warehousing etc.



Handling protection

TITAN 850

LEGENDS

EN388		MECHANICAL HAZARDS				
		PERFORMANCE LEVELS (X = NOT TESTED)				
4	1	3	2	X	P	
0-4	0-5	0-4	0-4	A-F	P	Impact protection (optional)
				Cut resistance according to ISO 13997		
				Puncture resistance		
				Tear resistance		
				Blade cut resistance		
				Abrasion resistance		

PRODUCT DETAILS

Interior finish	Seamless textile support
Gauge	13
Exterior finish	Ventilated back
Material	Nitrile GRIP&PROOF coating
Cuff characteristic	Large safety cuff
Colour.s	Black Red
European sizes	7 8 9 10 11

LOGISTIC DETAILS

Packaging	1 pair/bag 12 pairs/bag 48 pairs/carton
-----------	---

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/12/18/2899
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE

Edit 15/01/2025