

FEATURES

- Conductor stranding is flexible
- Oil resistant with temperatures up to 60°C
- Manufactured within the United Kingdom
- Variety of sheath colours
- Suitable for wiring circuits

RS PRO Black Tri-rated Cable, 1.5mm² CSA, 1kVdc, 600Vac, 21A, 100m

RS Stock No.: 180-5946



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Our RS Pro tri-rated cable has been designed to be used within electrical equipment, most commonly for wiring items that include power switchgear. The cable is also great for internal connections within rectifier equipment, motor starters, and controllers. Our RS PRO tri-rated cable range features highly durable wires that are made with flexible copper and are encased with a HR PVC (heat resistant polyvinyl chloride) insulation. The high maximum operating temperature of 105°C allows them to be used with a wide variety of applications such as electrical cabinets. RS PRO tri-rated cables are available in a variety of different coloured HR PVC sheaths including blue, black, red, brown, green, yellow and many more, to accommodate for a number of applications

General Specifications

Туре	Tri-rated
Tri-rated	Yes
Sheath Colour	Black
Fire Behaviour	Flame Retardant
Applications	Electrical cabinets, Industrial electrical installations, Small electronic devices, Relay and instrumentation panels, Control metering, Motor starters

Electrical Specifications

Voltage Rating	1kVDC, 600VAC
Current Rating	21A
Conductor Material	Annealed Copper
Insulation Material	PVC



Mechanical Specifications

Length	100m
Cross Sectional Area	1.5mm ²
Outer Diameter	3.3mm
Core Strands	30/0.25 mm
Size of Strands	0.25mm
Weight	23kg/km

Operation Environment Specifications

Maximum Operating Temperature	105°C
Maximum Conductor Temperature	60°C in oil

Approvals

Compliance/Certifications	CSA , UL ,BSI , RoHS Certificate Of Compliance
Standards Met	BS6231







Stock number:	180-5946	Black tri-rated cable 1.5mm 100m
	180-5947	Blue tri-rated cable 1.5mm 100m
	180-5949	Brown tri-rated cable 1.5mm 100m
	180-5969	Green tri-rated cable 1.5mm 100m
	180-5955	Green/yellow tri-rated cable 1.5mm 100m
	180-5953	Grey tri-rated cable 1.5mm 100m
	180-5952	Orange tri-rated cable 1.5mm 100m
	180-5945	Pink tri-rated cable 1.5mm 100m
	180-5950	Red tri-rated cable 1.5mm 100m
	180-5971	Violet tri-rated cable 1.5mm 100m
	180-5948	White tri-rated cable 1.5mm 100m
	180-5951	Yellow tri-rated cable 1.5mm 100m